

## Zack marker strip - ZB 5/WH-100:UNBEDRUCKT - 5060906

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Zack marker strip, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: snap into tall marker groove, for terminal block width: 5.2 mm, lettering field size: 5.15 x 10.5 mm

The figure shows various versions of the article

### Why buy this product

- Other pitches available on request
- The multi-section marking strips are easy to fit and can be easily separated if required
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves
- Unlabeled marking strips can be custom-labeled with a plotter or by hand

### Key Commercial Data

|                                      |                     |
|--------------------------------------|---------------------|
| Packing unit                         | 1 STK               |
| Minimum order quantity               | 100 STK             |
| GTIN                                 | <br>4 017918 096137 |
| GTIN                                 | 4017918096137       |
| Weight per Piece (excluding packing) | 1.120 g             |
| Custom tariff number                 | 39269097            |
| Country of origin                    | Germany             |

### Technical data

#### Dimensions

|           |      |
|-----------|------|
| Width (a) | 5 mm |
|-----------|------|

#### Ambient conditions

# Zack marker strip - ZB 5/WH-100:UNBEDRUCKT - 5060906

## Technical data

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

### General


|  |                                |
|--|--------------------------------|
| Note                                   | Can be labeled with CMS        |
| Color                                  | white                          |
| Type                                   | high                           |
| Components                             | free from silicone and halogen |
| Flammability rating according to UL 94 | V2                             |
| Material                               | PA                             |
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1)    |
|  | DIN VDE 0611                   |
| Number of individual labels            | 10                             |
| Number of individual labels per row    | 10                             |
| Number of marker strips                | 10                             |
| Marking mounting type                  | snap into tall marker groove   |

### Standards and Regulations

|  |                             |
|--|-----------------------------|
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1) |
|  | DIN VDE 0611                |
| Flammability rating according to UL 94 | V2                          |

## Drawings

Schematic diagram



## Classifications

eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
|------------|----------|

## Zack marker strip - ZB 5/WH-100:UNBEDRUCKT - 5060906

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |
| eCl@ss 9.0 | 27141137 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |
| ETIM 6.0 | EC000761 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131505 |

### Accessories

#### Accessories

#### Magazine

Magazine insert - CMS-P1-M/ZB - 5144699



Plastic magazines for CMS-P1-PLOTTER and PLOTMARK. For accommodating 22 zack marker strips