

A722 - Anti Impact Cut Resistant Glove

Collection: Impact protection

Range: Hand Protection

Materials: TPR, HPPE, Glass Fibre, Polyester, Nylon, Elastic

Dipping:

Inner Pack: 12

Outer Carton: 72

Product information

Combining comfort, grip, impact and cut resistance in a comfortable seamless liner. Flexible PVC impact pods and reinforced crotch for maximum durability. Suitable for heavy duty applications.

Impact protection

Hand injury is one of the most common and frequent complaints in the workplace. This collection of gloves provides vital protection against impact to the hand from multiple hazards.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwest's extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 3

EN 388: 2016 + A1: 2018 (4X43CP)

EN 407: 2020 (X1XXXX)

ANSI/ISEA 105: 2016 CUT Level (A4)

ANSI/ISEA 105: 2016 ABRASION Level (6)

ANSI/ISEA 138: 2019 Level 2



Features

- Maximum impact protection using TPR pod technology
- Level C cut resistance
- 13 gauge liner for a perfect fit
- Nitrile foam coating for excellent grip in wet and dry conditions
- Reinforced thumb crotch for extra protection and durability
- Wrist strap for secure fitting
- Double dipped coating for durability
- Breathable seamless liner
- Retail tag which aids presentation for retail sales
- ANSI cut level A4
- CE certified

A722 - Anti Impact Cut Resistant Glove
Commodity Code: 6116108091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/16728-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
A722G8RS	Grey/Black	43.0	28.0	50.0	0.1870	0.0602	5036108276974	15036108767066
A722G8RM	Grey/Black	43.0	28.0	50.0	0.2140	0.0602	5036108236152	15036108723987
A722G8RL	Grey/Black	43.0	28.0	50.0	0.2250	0.0602	5036108236145	15036108723970
A722G8RXL	Grey/Black	43.0	28.0	50.0	0.2290	0.0602	5036108236169	15036108723994
A722G8RXXL	Grey/Black	43.0	28.0	50.0	0.2530	0.0602	5036108276981	15036108767073
A722G8RXXXL	Grey/Black	43.0	28.0	50.0	0.2580	0.0602	5036108276998	15036108767080