## Cable lug assortment





## Metal case with 1100 crimp terminals 1.5...6 mm<sup>2</sup>

| Metal case with 1100 child terminals 1.50 him   |
|---|
| 50 x Partly insulated 0.5-1.5 mm <sup>2</sup> red double crimp female disconnectors 6.3 x 0.8 mm  |
| 40 x Partly insulated 1.5-2.5 mm <sup>2</sup> blue double crimp female disconnectors 6.3 x 0.8 mm |
| 30 x Partly insulated 4-6 mm <sup>2</sup> yellow double crimp female disconnectors 6.3 x 0.8 mm   |
| 50 x Partly insulated 0.5-1.5 mm <sup>2</sup> red double crimp male disconnectors 6.3 x 0.8 mm    |
| 40 x Partly insulated 1.5-2.5 mm <sup>2</sup> blue double crimp male disconnectors 6.3 x 0.8 mm   |
| 50 x Fully insulated 0.5-1.5 mm <sup>2</sup> red double crimp female disconnectors 6.3 x 0.8 mm   |
| 40 x Fully insulated 1.5-2.5 mm <sup>2</sup> blue double crimp female disconnectors 6.3 x 0.8 mm  |
| 50 x Fully insulated 0.5-1.5 mm <sup>2</sup> red double crimp female disconnectors 4.75 x 0.8 mm  |
| 50 x Partly insulated 0.5-1.5 mm <sup>2</sup> red double crimp female disconnectors 4.75 x 0.8 mm |
| 50 x Insulated 0.5-1.5 mm <sup>2</sup> red butt splice connectors 1.7 mm                          |
| 40 x Insulated 1.5-2.5 mm <sup>2</sup> blue butt splice connectors 2.5 mm                         |
| 30 x Insulated 4-6 mm <sup>2</sup> yellow butt splice connectors 3.4 mm                           |
| 50 x Red 4.3 mm ring terminals 0.5-1.5 mm <sup>2</sup>  |
| 40 x Blue 4.3 mm ring terminals 1.5-2.5 mm <sup>2</sup>   |
| 50 x Red 5.3 mm ring terminals 0.5-1.5 mm <sup>2</sup>  |
| 40 x Blue 5.3 mm ring terminals 1.5-2.5 mm <sup>2</sup>   |
| 50 x Red 6.4 mm ring terminals 0.5-1.5 mm <sup>2</sup>  |
| 40 x Blue 6.4 mm ring terminals 1.5-2.5 mm <sup>2</sup>   |
| 30 x Yellow 6.4 mm ring terminals 4-6 mm <sup>2</sup>   |
| 50 x Partly insulated 0.5-1.5 mm <sup>2</sup> red double crimp bullet disconnectors               |
| 50 x Fully insulated 0.5-1.5 mm <sup>2</sup> red double crimp receptacle disconnectors            |
| 40 x Partly insulated 1.5-2.5 mm <sup>2</sup> blue double crimp bullet disconnectors              |
| 40 x Fully insulated 1.5-2.5 mm <sup>2</sup> blue double crimp receptacle disconnectors           |
| 50 x Push-on blade 3 way (2 male tab) terminals 6.3 x 0.8 mm                                      |
| 50 x PCB male terminals 6.3 x 0.8 mm  |
| 1 x Fully insulated 3 male tab 6.3 mm   |
| 1 x Insulated 12 way double tab terminal 6.3 x 0.8 mm   |
| Crimping pliers are included  |
|   |

Art. Nr. RND 465-00048