


TWS Acoustic Sounder (IP54)



RND 430-00074 (12/48V)
RND 430-00075 (110/240V)

Dispositivo di segnalazione acustica.

Acoustic warning device.
Dispositif de signalisation
acoustique. Akustikmodul.
Zumbador.

CORPO BODY CORPS GEHAUSE CUERPO DEL PRODUCTO	PC										
GHIERA RING BAGUE RING CONTERA	PC										
GRUPPO ACUSTICO ACOUSTIC SOURCE SOURCE ACOUSTIQUE SCHALLQUELLE FUENTE SONORA	Buzzer										
COLORI DISPONIBILI AVAILABLE COLOURS COULEURS DISPONIBLES VERFÜGBARE FARBEN COLORES DISPONIBLES											
TENSIONE DI ALIMENTAZIONE VOLTAGE TENSION SPANNUNG TENSIÓN	12/48V ac/dc – 110/240V ac										
SERVIZIO OPERATION FONCTIONNEMENT BETRIEBSART FUNCIONAMIENTO	∞										
CORRENTE NOMINALE CURRENT CONSUMPTION CONSOMMATION DE COURANT STROMAUFNAHME CONSUMO DE CORRIENTE	<table border="1"><thead><tr><th></th><th>12Vac/dc</th><th>24Vac/dc</th><th>110Vac</th><th>240Vac</th></tr></thead><tbody><tr><td>mA (Max)</td><td>3</td><td>6</td><td>4</td><td>10</td></tr></tbody></table>		12Vac/dc	24Vac/dc	110Vac	240Vac	mA (Max)	3	6	4	10
	12Vac/dc	24Vac/dc	110Vac	240Vac							
mA (Max)	3	6	4	10							
RESA ACUSTICA ACOUSTIC OUTPUT RENDEMENT ACOUSTIQUE SCHALLLEISTUNGSPEGEL SALIDA ACUSTICA	Min 62dB(A) – Max 81dB(A)										
MODALITA' SUONO SOUND EFFECT EFFET ACOUSTIQUE SOUND- EFFEKT EFECTOS DE SONIDO	6 suoni (2800Hz) 6 sounds (2800Hz) 6 sons (2800Hz) 6 Ton (2800Hz) 6 sonidos (2800Hz)										
GRADO IP IP RATING DEGRE IP SCHUTZART GRADO IP	IP54										

TEMPERATURA DI FUNZIONAMENTO <i>OPERATING TEMPERATURE</i> <i>TEMPERATURE DE SERVICE BETRIEBSTEMPERATUR</i> <i>TEMPERATURA DE FUNCIONAMIENTO</i>	-30°C+50°C
VIBRAZIONI <i>VIBRATIONS</i> <i>VIBRATIONS</i> <i>VIBRATIONEN</i> <i>VIBRACIONES</i>	INDUSTRIAL CEI 60068-2-6 SINE
CERTIFICAZIONI, OMOLOGAZIONI <i>CERTIFICATIONS, APPROVALS CERTIFICACIONES,</i> <i>HOMOLOGATIONS PRODUKTZERTIFIKATE,</i> <i>ZULASSUNGEN CERTIFICADOS, HOMOLOGACIONES</i>	CE, UKCA
FISSAGGIO <i>MOUNTING</i> <i>FIXATION</i> <i>FIXIERUNG</i> <i>FIJACIÓN</i>	GHIERA <i>RING</i> <i>BAGUE</i> <i>RING</i> <i>CONTERA</i>
DISEGNO <i>TECHNICAL DRAWING</i> <i>DESSIN</i> <i>TECHNISCHE ZEICHNUNG</i> <i>DIBUJO TECNICO</i>	