

Socket Set, 123 Pieces



Features

- 123 piece socket and mechanic tool contains a huge range of sizes of sockets and wrenches to satisfy every need
- This set contains 1/2 inch, 3/8 inch, 1/4 inch ratchet handle and most daily useful sockets sizes, in standard and deep socket sizes
- Most popular sizes of extensions and adaptors are also included for various situations
- High Quality and Manufactured in chrome-vanadium steel for torque and durability, fully polished and chrome plated surfaces are used for anti rust
- Heat treated S2 screwdriver bits are perfect for industrial using



Kit Contents

3x CRV quick-release ratchet handle	1/4", 3/8", 1/2"
10x CRV sockets, 1/4" drive	4, 5, 6, 7, 8, 9, 10, 11, 12, 13 mm
4x CRV deep sockets, 1/4" drive	8, 9, 10, 12 mm
11x CRV sockets, 3/8" drive	9, 10, 12, 13, 14, 15, 16, 17, 18, 19 mm
4x CRV deep sockets, 3/8" drive	13, 14, 15, 17 mm
8x CRV sockets, 3/8" drive	8, 10, 11, 12, 14, 16, 18, 20 mm
7x CRV sockets, 1/2" drive	20, 21, 22, 24, 27, 30, 32 mm
3x CRV universal joints	1/4", 3/8", 1/2"
2x CRV adaptors	1/2" drive M X 3/8" Drive F, 1/4" Drive M X 3/8" Drive F
CRV coupler	1/4"
CRV spinner handle	1/4"
17x CRV bit sockets, 3/8" drive	T20, T30, T40, T45, T50, T55, T60, FD5.5, FD6.5, PH1, PH2, PZ1, PZ2, H3, H4, H5, H6
18x S2 screwdriver bits	25 mm
3x CRV spark plug sockets, 3/8 drive	14 mm, 16 mm, 21 mm
11x CRV combination spanners	8, 9, 10, 11, 12, 13, 14, 16, 17, 18, 19 mm
5x CRV extension bars	1/4" Dr.x50mm, 3/8"Dr.x75mm, 3/8"Dr.x150mm, 1/2" Dr.x125mm, 1/2"Dr.x250mm
CRV flex handle, 1/2" drive	250 mm
2x Chrome molybdenum screwdrivers	6X100 mm, PH2X100 mm
Oil filter wrench	1/2"
CRV 12.5 mm socket for cylinder	T52X100L
9-Piece CRV long hex key set	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10mm
Voltage Tester	
Blow mould case	

Art. Nr.

RND 550-00338