



# RUGGED® SSD

PROFESSIONAL USB-C SSD  
SOLUTION

Data Sheet

## Ultra Fast. Beyond Rugged.

LaCie Rugged® SSD offers filmmakers and DITs a substantial boost thanks to Seagate® FireCuda® NVMe speeds of up to 1050MB/s<sup>1</sup> with encryption plus dust, water, and drop resistance in a palm-sized solution. Enjoy spacious capacity of up to 4TB and seamless compatibility with Thunderbolt™ 3 and USB 3.2 Gen. 2 (USB-C) on both Mac® and Windows® computers.

- Transfer and edit RAW 4K video with speeds of up to 1050MB/s
- USB-C interface for universal compatibility
- IP67 rating for extreme dust and water resistance
- Three-meter drop and two-ton car crush resistance for extended durability
- Seagate Secure™ self-encrypting technology for project confidentiality
- Works with iPad - Connect your LaCie drive with USB-C
- Five-year limited warranty and Rescue Data Recovery Services<sup>3</sup>
- One-month complimentary membership to Adobe® Creative Cloud® All Apps Plan<sup>2</sup> for access to awesome photo and video editing apps



design by neil poulton

## Level Up Your 4K Video Project

Rugged SSD satisfies the cravings of filmmakers and DITs for high-speed transfers and editing power, extreme ruggedness, and password protection for utmost file security.

<sup>1</sup> Actual data rates may vary depending on operating environment and other factors, such as chosen interface and disk capacity.

<sup>2</sup> Membership to Adobe Creative Cloud All Apps plan is redeemable during product registration. Must redeem within one year of drive registration. Not available in China. For country list see <https://adobe.ly/cc-countries>. Internet connection and Adobe ID required. Available only to users 13 and older. See [www.adobe.com/legal.html](http://www.adobe.com/legal.html) for applicable terms and privacy policy.

<sup>3</sup> Rescue Data Recovery Services not available in all countries





## RUGGED® SSD

PROFESSIONAL USB-C SSD SOLUTION

Specifications				
Retail Packaging	Product Dimensions	Box Dimensions	Master Carton Dimensions	Pallet Dimensions
Length (in/mm)	0.669in/17mm	1.437in/36.5mm	7.559in/192mm	47.992in/1219mm
Width (in/mm)	2.555in/64.9mm	3.524in/89.5mm	6.142in/156mm	40.118in/1019mm
Depth (in/mm)	3.854in/97.9mm	5.709in/145mm	6.299in/160mm	42.913in/1090mm
Weight (lb/kg)	0.22lb/0.1kg	0.441lb/0.2kg	4.189lb/1.9kg	972.239lb/441kg
Quantities				
Boxes per Master Carton	8			
Master Cartons per Pallet	216			
Pallet Layers	6			

System Requirements	What's Included
<ul style="list-style-type: none"> <li>Interface: USB 3.2 Gen 2 (up to 10 Gb/s) USB-C</li> <li>Works with USB-C host: USB4, USB 3.0, Thunderbolt™ 4, Thunderbolt™ 3</li> <li>Compatible with most Windows and macOS systems. Visit <a href="https://lacie.com/os">lacie.com/os</a> for details<sup>1,2</sup></li> <li>Minimum free disk space: 600MB recommended</li> </ul>	<ul style="list-style-type: none"> <li>LaCie® Rugged SSD</li> <li>USB-C (USB 3.1 10Gb/s) cable</li> <li>Quick Install Guide</li> <li>One month Adobe® Creative Cloud® All Apps plan<sup>3</sup></li> <li>Rescue Data Recovery Services<sup>4</sup></li> </ul>

Region	Model Number	Capacity	Limited Warranty (years)	UPC Code	EAN Code	Multi-Pack UPC	Notes
WW	STHR500800	500GB	5	763649134245	3660619406715	10763649134242	NVMe SSD
WW	STHR1000800	1TB	5	763649134252	3660619406722	10763649134259	NVMe SSD
WW	STHR2000800	2TB	5	763649134269	3660619406739	10763649134266	NVMe SSD
WW	STHR4000800	4TB	5	763649169377	3660619042074	10763649169374	NVMe SSD

<sup>1</sup> Reformatting may be required for use with Time Machine

<sup>2</sup> Compatibility may vary depending on user's hardware configuration and operating system.

<sup>3</sup> One-month membership to Adobe Creative Cloud All Apps plan is redeemable during product registration. Must redeem within one year of drive registration. Not available in China. For country list see <https://adobe.ly/cc-countries>. Internet connection and Adobe ID required. Available only to users 13 and older. See [www.adobe.com/legal.html](https://www.adobe.com/legal.html) for applicable terms and privacy policy.

<sup>4</sup> Not available in all countries

LACIE.COM

© 2021 Seagate Technology LLC. All rights reserved. Seagate, Seagate Technology, LaCie, and the LaCie logo are registered trademarks of Seagate Technology LLC in the United States and/or other countries. FireCuda, Rugged, Seagate Secure, and the Seagate Secure logo are either trademarks or registered trademarks of Seagate Technology LLC or one of its affiliated companies in the United States and/or other countries. Adobe and Creative Cloud are either registered trademarks or trademarks of Adobe Systems Incorporated in the United States and/or other countries. Thunderbolt and the Thunderbolt logo are trademarks of Intel Corporation in the U.S. and/or other countries. All other trademarks or registered trademarks are the property of their respective owners. When referring to drive capacity, one gigabyte, or GB, equals one billion bytes and one terabyte, or TB, equals one trillion bytes. Your computer's operating system may use a different standard of measurement and report a lower capacity. In addition, some of the listed capacity is used for formatting and other functions, and thus will not be available for data storage. Actual data rates may vary depending on operating environment and other factors, such as chosen interface and drive capacity. The export or re-export of Seagate hardware or software is regulated by the U.S. Department of Commerce, Bureau of Industry and Security (for more information, visit [www.bis.doc.gov](https://www.bis.doc.gov)), and may be controlled for export, import, and use in other countries. Seagate reserves the right to change, without notice, product offerings or specifications. DS2016.4-2106US