

March, 2012

## 3M™ Super 77™ Multipurpose Spray Adhesive (Aerosol)

### Product Description

A high tack, high coverage and fast drying adhesive.

### Product Features

- A high tack, high coverage fast drying, transparent adhesive for permanently attaching foils, carpeting, many lightweight foams, paper, cardboard, felt and cloth to painted or unpainted metals, wood, hardboard and other base materials.
- It provides high initial "grab" with sufficient open time to allow for positioning of materials.
- Low soak-in gives better looking and higher coverage bonds.
- Soft, non-dimpling glue lines



# 3M™ Super 77™ Multipurpose Spray Adhesive (Aerosol)

## Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

## Typical Physical Properties

Property	Values	Notes
Color	Translucent	
Solids Content by Weight	25 %	
VOC	51 %	
Coverage	114 sq ft	@ 2.5 gms /ft <sup>2</sup> per lb (sqft)
Hazardous Air Pollutants (HAPS)	0.46 % by weight	
Spray Pattern	Mist	
Dry Time	15 to 60 s	Dry time will depend on ambient temperature, humidity and coverage applied.
Shear Adhesion Failure Test - SAFT	150 °F	SAFT Shear Adhesion Failure Test with birch plywood, 1 inch overlap, 100 grams used, temperature start at 90°F and ramped 10°F every 10 min. until complete failure.
Flammable Solvent	Yes	
Flammable Propellant	Yes	
Base	Synthetic Elastomer	
Bonding Range	15 sec - 15 min	

## Typical Uncured Physical Properties

**Density:** 6 lb/gal

## Available Sizes

Container Size	3M Stock Number	UPC Number
24 Fl. Oz. (Net Wt. 16.75 oz)	62-4977-4930-9	00-021200-21210-9
Large Cylinder – 29.3 lbs.	62-4979-8030-0	00-051115-25776-6
5 gallon pail – 32.5 lbs.	62-4458-8530-4	00-021200-43793-9
52 gallon drum – 338 lbs.	62-4458-9530-3	00-021200-43813-4

## Storage and Shelf Life

Store product at 60-80°F (16-27°C) for maximum storage life. Higher temperatures reduce normal storage life. Lower temperatures may cause increased viscosity of a temporary nature. Rotate stock on a “first in-first out” basis.

When stored at the recommended conditions in original, unopened container, this product has a shelf life of 18 months from date of manufacture.

# 3M™ Super 77™ Multipurpose Spray Adhesive (Aerosol)

## Trademarks

3M is a trademark of 3M Company.

The GREENGUARD INDOOR AIR QUALITY CERTIFIED Mark is a registered certification mark owned by Air Quality Sciences, Inc. and used under license through the Greenguard Environmental Institute.

LEED® is a registered trademark of the United States Green Building Council (USGBC).

## References

Property	Values
3m.com Product Page	<a href="https://www.3m.com/3M/en_US/company-us/all-3m-products/-/3M-Super-77-Multipurpose-Spray-Adhesive/?N=5002385+3293242460&amp;rt=rud">https://www.3m.com/3M/en_US/company-us/all-3m-products/-/3M-Super-77-Multipurpose-Spray-Adhesive/?N=5002385+3293242460&amp;rt=rud</a>
Safety Data Sheet SDS	<a href="https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&amp;msdsLocale=en_US&amp;co=ptn&amp;q=77 Multipurpose Spray Adhesive">https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&amp;msdsLocale=en_US&amp;co=ptn&amp;q=77 Multipurpose Spray Adhesive</a>

## Family Group

	77 Multipurpose Spray Adhesive	77 Cylinder Spray Adhesive	77 Spray Adhesive (Bulk)
Color	Translucent	Translucent	Translucent
Solids Content by Weight (%)	25	27	36
Spray Pattern	Mist	Mist	Mist

## Precautionary Information

Refer to product label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

# 3M™ Super 77™ Multipurpose Spray Adhesive (Aerosol)

## Information

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

