

2 Port USB HDMI KVM Switch with Audio and USB 2.0 Hub

Product ID: SV231HDMIUA



The SV231HDMIUA 2-port USB HDMI KVM Switch lets you control two USB-enabled multimedia computers or devices with HDMI video interfaces, using a single peripheral set/console (USB keyboard, mouse, monitor, speakers and microphone).

A highly versatile KVM solution, the USB HDMI KVM Switch features an integrated 2-port USB 2.0 hub that lets selected computers access shared high speed USB devices, eliminating the cost of duplicate USB peripheral purchases.

Ensuring high quality video capability, the HDMI KVM switch supports HD resolutions of up to 1920 x 1200. Offering genuine digital signal transmission over the cable, this switch can be used to share one HD panel between multiple HDMI sources such as Blu-Ray players, Video Game consoles and HD media centers.

The switch also supports audio and microphone switching functions and allows you to select connected computers, USB device hub ports and audio/mic channels either simultaneously or independently using either front-panel push-buttons or keyboard hotkeys.

This product is TAA compliant and backed by a Startech.com 3-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for sharing two newer HDMI multimedia PCs with an HDMI monitor
- Students can use a single monitor and connect their gaming console along side their PC or laptop
- Allows multimedia PCs to share peripherals and a single high definition television



• Use in the Office to connect two multimedia PCs to a single console connection increasing productivity

Features

- Supports push button and hotkey PC Switching
- Integrated USB 2.0 hub Share USB peripherals between PCs
- Supports High Resolutions Digital video up to UXGA (1600x1200), WUXGA (1920x1200), and 1080p (1920x1080)
- No software drivers required; OS independent
- Supports Plug&Play operation
- Supports both HDMI audio and 3.5mm analog audio

On-Screen Display

No

- Independent Audio switching
- Audible tone to indicate PC switching
- User-defined scan time intervals

Prominence		
	Warranty	3 Years
	Description CDW 75 - 1st Line	StarTech.com 2 Port USB HDMI KVM Switch with Audio and USB 2.0 Hub - KVM /
Hardware		
	Audio	Yes
	KVM Ports	2
	PC Interface	USB
	PC Video Type	HDMI
	Number of Monitors Supported	1
	Rack-Mountable	No
	Cables Included	No
	Daisy-Chain	No



IP Control No

Hot-Key Selection Yes

Maximum Digital Resolutions

1920 x 1200

Wide Screen Supported Yes

Maximum Number of

Users

1

Port Selection Support Push Button and Hotkeys

MTBF 126813 hours

Connector(s)

Console Interface(s) HDMI (19 pin)

USB Type-A (4 pin) USB 2.0

3.5 mm Mini-Jack (3 Position)

Host Connectors HDMI (19 pin)

USB B (4 pin)

3.5 mm Mini-Jack (3 Position)

Software

OS Compatibility OS independent; No software or drivers required

Indicators

LED Indicators Online/Active (Green - Connected PC is online, Red - PC is selected)

Power

Power Source AC Adapter Included

Input Voltage 100 - 240 AC

Input Current 0.8A

Output Voltage 12V DC

Output Current 1.5A

Center Tip Polarity Positive

Plug Type M



Power Consumption (In 1

Watts)

Environmental

Operating Temperature 0C to 40C (32F to 104F)

Storage Temperature -20C to 60C (-4F to 140F)

Humidity 0~80% RH

Physical Characteristics

Color Black

Material Steel

Product Width 4.9 in [12.5 cm]

Product Height 1.6 in [40 mm]

Product Depth 2.8 in [70 mm]

Weight of Product 22.4 oz [634 g]

Packaging Information

Package Length 9.8 in [25 cm]

Package Width 7.4 in [18.8 cm]

Package Height 3.9 in [100 mm]

Shipping (Package)

Weight

2.4 lb [1.1 kg]

What's in the Box

Included in Package 2 Port HDMI KVM

Package of Rubber feet

Power Adapter

User Manual

^{*}Product appearance and specifications are subject to change without notice.