



A CORNERSTONE FOR STORAGE

Stream S07 | 3.5" External Hard Drive

Storage Space For Years To Come

What would you do with up to 8TB of extra storage capacity?

That's up to 1.3 million photos (6MB per photo), 2 million songs (4MB per song), 800 Full-HD movies (10GB per movie), or 3.2 million e-books (2.5MB per e-book). Needless to say, it's a whole lot of storage space for years to come. At the same time, you'll improve your device's performance by freeing up space on its internal hard drive when transferring it to the Stream S07.



up to **8TB**

'Cracked' With A Purpose

The Stream S07 was carefully designed after a stone, a symbol of durability and longevity. And just like a stone that's been tested through time, it has a crack. But this crack is intentional – it has a dual purpose. First, it serves as a ventilation source to keep the drive running cool. Second, with built-in neon blue LED lights, it serves as a transfer status indicator that runs through the crack, illuminating it while processing data.



3.5" External Hard Drive

Stream S07

Features

- Extremely high storage capacity options, up to 8TB
- Super-speed data transfer with USB 3.2 Gen 1 interface (up to 5Gbps)
- As a storage expansion, free up space on your device's internal hard drive and improve its performance
- Exclusive ventilation holes permit an incredible cooling effect and makes it suitable for high-temperature entertainment center environments
- Thoughtfully designed drive can be placed either upright or flat for flexible configuration options
- Connect it to your Smart TV and record all of your favorite movies and TV shows directly on to the drive and play them back whenever you like
- Uniquely designed LED indicator makes it easier for users to gauge the transfer status
- Power saving sleep mode enabled for when the drive is not in use
- Free SP Widget software available for download to provide powerful functions such as data backup and restore, AES 256-bit encryption, and cloud storage for efficient data management

3TB | 4TB | 6TB | 8TB

Specifications

- Capacity: 3TB, 4TB, 6TB, 8TB
- Dimensions: 171.0mm x 113.6mm x 34.9mm
- Weight: 681g - 941g (by capacity)
- Material: Plastic
- Color: Black
- Interface: USB 3.2 Gen 1 (USB 3.1, USB 3.0, and USB 2.0 backwards-compatible)
- OS Compatibility: Windows 10/8.1/8/7/Vista/XP 64-Bit, Mac OS 10.5.x, Linux 2.6.x
- Operating Temperature: 5°C - 45°C
- Storage Temperature: -40°C - 70°C
- Operating Voltage: DC12V
- Certification: CE, FCC, BSMI, Green dot, WEEE, RoHS
- Warranty: 3 years