

# ENSTO

## SPCM131815G

### Cubo S enclosure

Code	SPCM131815G
GTIN	6418677166440
Name	Cubo S enclosure Ensto Cubo S Size 125 x 175 x 150 mm, 50 mm base, metric knockouts, grey cover, PC
Description	Ensto Cubo S is a series of small to medium size enclosures available with knockouts or plain sides. The base of the enclosures is equipped with unique slots for printed circuit boards.



## Technical specification

### Technical specification

<b>Content:</b>	Enclosure base, cover, cover screws, mounting screws
-----------------	---

### Dimensions

<b>Weight:</b>	0.60 kg
<b>Width:</b>	125 mm
<b>Volume :</b>	328.13 cm <sup>3</sup>
<b>Size:</b>	125 x 175 x 150
<b>Height:</b>	175 mm
<b>Depth:</b>	150 mm
<b>Inner depth:</b>	135.5 mm
<b>Outer base depth:</b>	50 mm
<b>Outer cover height:</b>	100 mm

### Temperatures

<b>Operating temperature:</b>	-40 ... +80 °C
<b>Short term temperature range:</b>	-40 ... +120 °C

### Materials

<b>Base:</b>	Fiberglass reinforced polycarbonate
<b>Cover:</b>	Polycarbonate

<b>Cover screws:</b>	Polyamide
<b>Gasket:</b>	Polyurethane
<b>Material selection:</b>	Polycarbonate

## Colors

<b>Color:</b>	Grey
---------------	------

## Features

<b>Knockouts:</b>	4 x M16/25 + 8 x M12/20
-------------------	-------------------------

## Mechanical

<b>Impact strength:</b>	IK 08
-------------------------	-------

## Certificates

<b>Standards:</b>	EN 62208, GOST R
-------------------	------------------

## Ratings

<b>Degree of protection:</b>	IP66/IP67
<b>Flammability rating:</b>	UL 746C 5 inch flame test
<b>ETIM class:</b>	EC000261

## ETIM

---

### ETIM

<b>Width:</b>	125 mm
<b>Colour:</b>	Grey
<b>Material:</b>	Plastic
<b>Height:</b>	175 mm
<b>Depth:</b>	150 mm
<b>Type of surface:</b>	Untreated
<b>RAL-number:</b>	7035
<b>Wall fastening possible:</b>	true
<b>Suitable for outdoor set-up:</b>	true
<b>Impact strength:</b>	IK08
<b>Degree of protection (IP):</b>	IP67
<b>Pole fastening:</b>	false
<b>With glazed door:</b>	false
<b>Tackable:</b>	false
<b>Wall build in:</b>	false
<b>Pitched roof:</b>	false
<b>EMC-version:</b>	false
<b>With ventilation door:</b>	false
<b>With backside door:</b>	false
<b>Floor installation possible:</b>	false

## Packaging

---

### Default package

<b>Unit:</b>	PCS
<b>Size:</b>	1