

Combo Card Reader _ Two For One With SP's New Combo Card Reader _ Silicon Power

 silicon-power.com/web/gb/product-Combo



The Dynamic Duo Of Card Slots

Dual SD/MMC and microSD card slots make this compact combo card reader a force to be reckoned with! It requires no software or driver installation with Plug & Play technology and seamlessly works across all major operating systems: Windows, Mac OS, Linux, and Chrome OS. It's the most efficient way to transfer content from your memory cards.



Quick Transfers On The Fly

With a USB 3.2 Gen 1 Type-A interface, this combo card reader provides up to 5Gbps of bandwidth for quick transfers so you can move content faster and get back to what you love doing sooner. That's up to 10 times faster than USB 2.0! But, it's also backwards-compatible with USB 2.0 too, which is particularly helpful for systems with limited USB 3.2 ports.

Details That Simplify The Task

The ergonomic (and stylish) design of this combo card reader makes it easy to insert and retrieve from your systems. It's also powered directly from the USB port so no external power source is required and it has a handy built-in LED indicator that provides data transfer activity status. Put simply, it doesn't get more convenient than this.

Ready To Go

A small and compact design is the perfect complement to this combo card reader's capabilities. Whatever device you're using, from drones to dash cams or GPS receivers to DSLR cameras, its portable-friendly size makes it an ideal companion to quickly offload footage onto smartphones, laptops, and tablets anywhere.

The Card Reader Edge

Card readers provide advantages that memory cards can't achieve alone. This combo card reader saves the battery on your devices, as they usually transfer data at the expense of their own battery when used directly. Also, it often provides higher read and write speeds for your cards versus when they are connected through your devices. It's a win-win situation!

Specifications



- Dimensions
- 61.5mm x 34.0mm x 12.5mm
- Weight
- 16.7g
- Material
- Plastic
- Color
- Black, White
- Input
- USB Type-A (USB 3.2 Gen 1)
- Output
- SD/MMC Card (x1), microSD Card (x1)
- Supported OS
- Windows® 10/8.1/8/7/Vista/XP, Mac™ OS 10.X+, Linux™ Kernel 2.4X/2.6X, Chrome OS™
- Operating Temperature
- 0°C - 55°C
- Storage Temperature
- -20°C - 70°C
- Humidity
- 10% - 90%

- Certification
- CE, FCC, BSMI, UKCA, KC

- Warranty
- 2 years limited warranty

Features

- Combo card reader supports the most commonly used memory card formats with dual SD/MMC and microSD card slots* -SD/MMC Slot: SD, SDXC, SDHC, MMC - microSD Slot: microSD, microSDXC, microSDHC
 - *Supports the usage of only one card slot at a time
- USB 3.2 Gen 1 Type-A interface provides up to 5Gbps of bandwidth for quick data transfers between the card reader and peripherals - up to 10 times faster than USB 2.0
- Backwards-compatible with USB 2.0 (up to 480Mbps of bandwidth) which is convenient for systems with limited USB 3.2 ports
- Seamlessly works across all major operating systems: Windows, Mac OS, Linux, and Chrome OS
- Supports SD/microSD cards with up to 2TB storage capacity
- Supports Secure Digital v3.01 UHS-I DDR200 speed mode
- True Plug & Play technology: no software or driver installation needed
- Powered directly from the USB port: no external power source required
- Compact size is portable-friendly for convenient access to card data anywhere
- Built-in LED indicator provides data transfer activity status

Combo

All

- SPU3AT5REDEL300W
- SPU3AT5REDEL300K