

2 Port USB C KVM Switch - 4K 60Hz HDMI - Compact Dual Port UHD USB Type C Desktop Mini KVM Switch with USB C Cables - Bus Powered - MacBook iPad Pro ThinkPad IdeaPad EliteBook

Product ID: SV211HDUC



This 2-port USB-C KVM enables you to easily switch between two USB Type-C or Thunderbolt 3 desktop or laptop computers, using a single keyboard, HDMI monitor and mouse.

Utilizing USB-C with DP alt-mode, this compact KVM switch only requires a single cable be connected to each of your computers, ensuring a small footprint with limited cabling requirements. All required cables for connecting your computers are included, to ensure a hassle-free setup right out of the box.

For easy operation, the KVM features a single button that toggles between connected computers.

The USB-C KVM switch supports UHD resolutions up to 4K (3840x2160) at 60Hz and can drive one large HDMI 2.0 display with ease, maximizing viewing space.

Along with the USB-C design that ensures cabling requires are minimum the KVM is bus powered further reducing clutter by avoiding the need for a bulky power adapter. The lightweight small form factor makes this mini KVM switch easy to deploy and is ideal for mobile/hot desk workforces.

The KVM is OS independent supporting all operating systems including Windows, Linux, macOS, iPadOS (Apple iPad Pro) and Android. StarTech.com has rigorously tested this product to ensure compatibility with all popular device brands including: Dell, HP, Apple and Lenovo.

The SV211HDUC is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- High resolution medical imaging

- Digital signage server control
- Mobile and hot-desk work forces

Features

- **SPACE-SAVING:** Compact USB C KVM switch enables easy switching between 2 USB Type C or Thunderbolt 3 desktops/laptops using 1 keyboard, monitor & mouse; OS independent and works with the Apple iPad Pro
- **2 PORT USB-C KVM:** 4K 60Hz UHD 3840x2160 HDMI 2.0 Out Push-Button Switching Bus Powered OS Independent Works with Thunderbolt 3 ports Cables included
- **PORTABLE:** USB powered feature reduces clutter by avoiding the need for power adapter while the lightweight small form factor makes the mini KVM Switch easy to carry for the mobile/ hot desk workforce
- **READY TO USE:** USB-C cables for host computers are included w/ the dual port KVM switch, providing easy to deploy solution straight out of the box; works w/popular brands like Dell, HP, Apple & Lenovo
- **THE STARTECH.COM ADVANTAGE:** StarTech.com offers a 2-year warranty and free lifetime 24/5 multilingual technical support based in North America on this 2 port KVM switch

Prominence

Warranty	2 Years
Description CDW 75 - 1st Line	StarTech.com 2 Port USB C KVM Switch - UHD 4K 60Hz HDMI w/USB Type C Cables

Hardware

Audio	Yes
KVM Ports	2
PC Interface	USB-C
PC Video Type	USB-C (DP Alt-Mode)
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Chipset ID	Parade - PS176 VLI - VL170 Terminus - FE1.1S

Daisy-Chain No

Performance

Video Revision DisplayPort 1.2

HDMI 2.0

On-Screen Display No

IP Control No

Hot-Key Selection No

Maximum Data Transfer Rate 480Mbps

Wide Screen Supported Yes

Audio Specifications HDMI - 7.1 Channel Audio

Port Selection Support Push Button

MTBF 50,000 hours

Connector(s)

Console Interface(s) USB Type-A (4 pin) USB 2.0

HDMI (19 pin)

Host Connectors USB Type-C (24-pin) USB 2.0 (480Mbps)

Special Notes / Requirements

System and Cable Requirements Your USB-C ports must support DisplayPort over USB-C (DP Alt mode) in order to work with this KVM switch

Indicators

LED Indicators Functional Display

Port selection or active host

Power

Power Source Bus Powered

Environmental

Operating Temperature 5C ~ 35C



Storage Temperature	-20C ~ 50C
Humidity	20%RH ~ 80%RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	5.5 in [14.0 cm]
Product Width	2.8 in [72.0 mm]
Product Height	0.6 in [15.7 mm]
Weight of Product	11.2 oz [318.0 g]

Packaging Information

Package Length	6.9 in [17.5 cm]
Package Width	4.7 in [12.0 cm]
Package Height	3.3 in [85.0 mm]
Shipping (Package) Weight	15.8 oz [448.0 g]

What's in the Box

Included in Package	KVM Switch
	3.3 ft. [1 m] USB-C Cables
	Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***

