

12U 19in Desktop Open Frame 2 Post Rack

Product ID: RK12OD



The RK12OD 12U 19in Desktop Open Frame 2 Post Rack provides the perfect mounting option for smaller Audio/Video and IT equipment where space is limited and a full sized cabinet is not required. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The 12U rack features a compact and lightweight free-standing design that is suitable for installation on or around your desk giving you easy access to the mounted equipment in your workspace. This lightweight 2 post rack is engineered to meet EIA rack mount standards and includes a pack of 20 M5 screws and Cage Nuts, allowing you to mount up to five devices into the rack right away.

Backed by a StarTech.com lifetime warranty.

Certifications, Reports and Compatibility

Applications

• Mount patch panels, network switches, and routers in small or home office networks or IT offices to provide easy access to equipment

- Mount KVMs and rack-mount computer/server systems neatly on or beside your desk
- Mount AV equipment such as broadcast/distribution devices, switches or extenders

Features

Includes 20 M5 Screws and Cage Nuts for mounting devices



- Easy to assemble
- TAA compliant for GSA Schedule purchases
- Lightweight design for easy relocation
- Meets EIA standards

Hardware		
	Warranty	Lifetime
	Wallmountable	No
	Rack Type	2-Post
	Frame Type	Open Frame
	U Height	12U
	Special Features	Easy Assembly
	Mounting Rail Profile	G-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance	Weight Capacity	110.5 lb [50 kg]
Physical Characteristics		
	Color	Black
	Construction Material	Steel
Product Measurements		
	Product Length	11.5 in [29.2 cm]
	Product Width	19.8 in [50.3 cm]
	Product Height	23.1 in [58.6 cm]
	Weight of Product	5.6 lb [2.6 kg]
	Maximum Mounting Depth	13.5 in [34.3 cm]



Packaging Information		
	Flat Pack (Assembly Required)	Yes
	Package Length	24.0 in [61 cm]
	Package Width	6.5 in [16.4 cm]
	Package Height	3.9 in [99 mm]
	Shipping (Package) Weight	6.8 lb [3.1 kg]
What's in the Box		
	Included in Package	12U Vertical Post
		Legs
		Base Bracket
		Package of assembly hardware (8 Screws)
		M5 Screws
		M5 Cage Nuts
		Rubber Feet
-		

*Product appearance and specifications are subject to change without notice.

