

8U 19" Wall Mount Network Rack - 12" Deep 2 Post Open Frame Server Room Rack for Data/AV/IT/Computer Equipment/Patch Panel with Cage Nuts & Screws 135lb Capacity, Black

Product ID: RK812WALLO



The RK812WALLO 8U Open Frame Wall Mount Equipment Rack (12in Depth) is a high quality, low cost relay rack that is easy to assemble and install into any environment. The rack can be wallmounted or installed as a free standing storage solution. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Able to accommodate common networking, audio-video and telecom equipment, the open rack offers a depth of 12in; the wall mounts are positioned 16in apart (center to center), making it suitable for mounting on virtually any wall surface, based on North American wall frame stud spacing standards.

This 8U rack can be mounted to the wall in a server room, office, or above a doorway, expanding your workspace and keeping your equipment easily accessible.

Backed by a StarTech.com lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mounting Audio Video broadcast or distribution components

Features



- STURDY & CONVENIENT: 8U 19" Open Frame wall mount network rack with 12" mounting depth is EIA/ECA-310 compatible & supports like patch panels, shelves and unmanaged switches
- HEAVY DUTY: This heavy duty 2 post open frame rack supports unobstructed airflow & is easy to install with a durable design made from SPCC cold-rolled steel with support for up to 135lbs of equipment
- EASY ASSEMBLY: The rack ships flat packed with ISTA-6 certified packaging to ensure complete and undamaged delivery and also features comprehensive assembly instructions
- ACCESSORIES INCLUDED: The wall mount server room/ computer/communication/AV/IT equipment rack includes a complete set of screws and cage nuts to securely mount all of your equipment in the rack
- STARTECH.COM ADVANTAGE: IT professionals' choice for over 30 years; our 2-post wall mount network racks backed for life by StarTech.com, including free 24/5 North America based multi-lingual tech support

Hardware		
	Warranty	Lifetime
	Wallmountable	Yes
	Rack Type	2-Post
	Frame Type	Open Frame
	U Height	8U
	Special Features	Easy Assembly
		Wall-Mountable
	Mounting Rail Profile	G-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance		
	Weight Capacity	176.8 lb [80 kg]
Physical Characteristics		
	Color	Black
	Construction Material	Steel
Product Measurements		
	Product Length	11.9 in [30.3 cm]



Product Width 19.8 in [50.3 cm]

Product Height 17.8 in [45.1 cm]

Weight of Product 15.0 lb [6.8 kg]

Maximum Mounting Depth 11.8 in [30 cm]

Packaging Information

Flat Pack (Assembly

Required)

Yes

Package Length 25.6 in [65.0 cm]

Package Width 21.8 in [55.4 cm]

Package Height 4.1 in [10.4 cm]

Shipping (Package)

Weight

18.1 lb [8.2 kg]

What's in the Box

Included in Package 8U Rack

M5 Screws

M5 Cage Nuts

Assembly Screws

Installation Guide

^{*}Product appearance and specifications are subject to change without notice.