

20m USB 2.0 Active Extension Cable - M/F

Product ID: USB2AAEXT20M



The USB2AAEXT20M 20m Active USB 2.0 Extension Cable offers one USB-A male connector and one USB-A female connector, and provides an active extension of USB 2.0 devices of up to 20-meters (66-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations, the active USB 2.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the length limits of standard USB cables. Plus you can daisy chain 2 cables for a total USB extension of up to 40-meters.

If necessary, the USB device can be powered from a wall outlet using the Universal AC power adapter (provided with the cable).

The USB2AAEXT20M repeater cable supports the full USB 2.0 bandwidth of 480 Mbps, and is backed by StarTech.com's 2-year Warranty.

Certifications, Reports and Compatibility

Applications

- Extend the distance of USB peripherals beyond the USB 2.0 5-meter limitation
- Daisy chain 2 cables together for even longer USB extensions

Features

- USB bus-powered
- Universal external power source also included

- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring
- Fully shielded for error-free connections
- Plug-and-play, no driver required
- Compatible with PC Windows 8/7/Vista/XP and Mac computer systems

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
Connector B	USB Type-A (4 pin) USB 2.0

Special Notes / Requirements

Note	Cascade two USB2AAEXT20M devices together for further extension
------	---

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.35 A
Output Voltage	5 DC
Output Current	1A
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	5

Environmental

Operating Temperature	0C to 70C (32F to 122F)
Storage Temperature	-20C to 85C (-4F to 185F)



Physical Characteristics

Color	Black
Cable Length	65.6 ft [20 m]
Product Length	65.6 ft [20 m]
Weight of Product	30.6 oz [866 g]

Packaging Information

Package Quantity	1
Package Length	6.8 in [17.2 cm]
Package Width	5.8 in [14.8 cm]
Package Height	4.8 in [12.2 cm]
Shipping (Package) Weight	35.1 oz [993 g]

What's in the Box

Included in Package	20 m USB 2.0 Active Extension Cable - M/F
	Universal Power Adapter
	Plug Adapters for North America, UK, Europe, and Australia

****Product appearance and specifications are subject to change without notice.***

