

TowerLine accessories

① Perforated panels

	Module	Order No
Perforated panel	M48 x 15.32"	861533-49
Perforated panel	M60 x 15.32"	861526-49
Perforated panel	M72 x 15.32"	861531-49
Corner perforated panel		890411-49

② Steel shelves

	Module	Order No
Steel shelf	M48 x 11.81"	854480-49
Steel shelf	M48 x 15.75"	854483-49
Steel shelf	M60 x 11.81"	854481-49
Steel shelf	M60 x 15.75"	854484-49
Steel shelf	M72 x 11.81"	854482-49
Steel shelf	M72 x 15.75"	854485-49
Corner steel shelf		854479-49
Divider pair for shelves		861116-49

Light / balancer rail

	Module	Order No
Light / balancer rail	M48	91849010
Light / balancer rail	M60	91849006
Light / balancer rail	M72	91849008

LED Lights


	Order No
24" dual intensity LED light fixture, light balancer rail hardware	14-95035151
36" dual intensity LED light fixture, light balancer rail hardware	14-95035152
48" dual intensity LED light fixture, light balancer rail hardware	14-95035153
24" dual intensity LED light fixture, with magnetic attachment	14-95035154
36" dual intensity LED light fixture, with magnetic attachment	14-95035155
48" dual intensity LED light fixture, with magnetic attachment	14-95035156

③ Drawer units 45 (in the picture 45/26-1)

Model	Outer dims W x D x H inches	Drawers	Opening	Max load lbs./drawer	Order No
45/14-1	17.72" x 20.47" x 5.51"	1 x 3.94"	100%	132	60349001
L-45/14-1	17.72" x 20.47" x 5.51"	1 x 3.94"	75%	66	60349002
45/26-1	17.72" x 20.47" x 10.24"	2 x 3.94"	100%	132	60449001
L-45/26-1	17.72" x 20.47" x 10.24"	2 x 3.94"	75%	66	60449002
Drawer unit attachment bracket					854463-49

Horizontal dividers

	Order No
4 x horizontal divider	872982-49
Drawer 45/3.94"	872982-49
Drawer 45/5.91" and 45/7.87"	872983-49



Bin rail

	Module	Order No
Bin rail	M48	859157-49
Bin rail	M60	859154-49
Bin rail	M72	859155-49

Footrest

	Order No
Footrest for spacer bar attachment	860551-49




Horizontal cable trough

	Module	Order No
Horizontal cable trough	M48	854555-49
Horizontal cable trough	M60	854556-49
Horizontal cable trough	M72	854557-49

Holders and trays

	Size W x D inches	Order No
④ CPU holder	7.09"-8.86" x 17.72" x 1.97"	860740-49
⑤ LCD holder with with 2.36" double arm		93049002
TowerLine arm holder for 2.36" arm*		861099-49
Keyboard tray for LCD holder	18.9" x 10.24"	860941-49
⑥ Keyboard tray (attached to bench top)	24.8" x 15.75"	92549001
⑦ Document holder A4 with 1.57" arm	11.42" x 12.99"	92849008
TowerLine arm holder for 1.57" arm**		861098-49

* Needed for accessories with 2.36" arms; ** Needed for accessories with 1.57" arms



Power Rails

	Order No
M48 Bin rail w/6 outlet power	14-9114915
M60 Bin rail w/6 outlet power	14-9114919
M72 Bin rail w/6 outlet power	14-9114923
Under surface 6 outlet power	14-91135133