



DOCKING STATION

DELL UNIVERSAL DOCK – UD22

Get a seamless consistent docking experience for any USB-C laptop, with fast charging, highest number of ports¹ and highest number of display supports for a universal dock.¹



DELL UNIVERSAL DOCK – UD22



Seamless Experience

The ultimate universal dock, it offers the same experience for all USB-C notebooks regardless of the operating system and the manufacturer. Get started quickly even if the DisplayLink drivers are not installed, thanks to the additional support for Hybrid DP Alt mode.



Uncompromised Productivity

Create a productive environment with enhanced flexibility with the highest number of ports on a universal dock¹. Connect multiple devices and displays with 4 x USB-A ports, 2 x USB-C ports and 4 video ports.



Intelligent Management


Intelligent management capabilities make it easier to deploy, manage and upgrade the docks in your environment. Streamline the deployment and management of all the docks with a single firmware.



DELL UNIVERSAL DOCK – UD22

Limitless compatibility.

The ultimate universal dock for any USB-C notebook, with fast charging, highest number of display support¹, and the highest number of ports¹, it allows you to create your workspace the way you like it.



...
Universal Docking Solution:
UD22 works with all USB C notebook and delivers a consistent experience regardless of the OS or the manufacturer of the laptop.

...
High Power Delivery:
With up to 96W power delivery for all laptops, all laptops can get the same fast charging experience as Dell systems.

...
Highest number of display support:
With the ability to connect up to 4 4K displays, users can multitask and maximize their productivity.

...
Highest number of ports:
With more ports than other universal docks, get enhanced flexibility to connect to multiple devices and displays to create the workstation for your requirements.

...
Dual support with Hybrid USB-C connectivity:
Get started quickly even if DisplayLink drivers are not installed, with Hybrid DP Alt Mode.

...
3 Year warranty with option to extend to 5 Years:
Dell Docks now have their own service tags for better support.

...
Intelligent management capabilities:
Easier to deploy, manage and upgrade the docks in at the hybrid work environment.

DOCKING STATIONS

DELL UNIVERSAL DOCK – UD22

FEATURE TECHNICAL SPECIFICATION

MODEL	Dell Universal Dock – UD22
PRODUCT TYPE	Docking Station
DISPLAY SUPPORT	If PC has DisplayLink drivers installed: For a HBR2* PC 2 x 4K @ 60Hz + 2 x FHD @60Hz 2 x 4K @ 60Hz + 1 x 4K @30Hz For a HBR3 PC 2 x 4K @ 60Hz + 2 x QHD @60Hz 2 x 4K @ 60Hz + 1 x 4K @30Hz For HBR3 PC (supporting Display Stream Compression) 4 x 4K @ 60Hz If PC does not have DisplayLink drivers installed ¹ : For a HBR2 PC 2 x FHD @60Hz 1 x 4K @ 30Hz For a HBR3 PC 2 x QHD @60Hz 2 x 4K @ 30Hz For HBR3 PC (supporting Display Stream Compression) 2 x 4K @ 60Hz
MAX RESOLUTION	5K @ 60Hz with HBR3 systems supporting Display Stream Compression
VIDEO INTERFACES	1 x HDMI 2.0 2 x DP 1.2 1 x USB-C 3.2 Gen2 with DisplayPort 1.4 Alt Mode
USB PORTS	USB-A: 4 x USB 3.2 Gen 2 (1 with PowerShare) USB-C: 1 x USB 3.2 Gen 2 with PowerShare; 1 x USB 3.2 Gen 2 with DisplayPort 1.4 Alt Mode
NETWORKING	Gigabit Ethernet
SECURITY SLOT TYPE (CABLE LOCK SOLD SEPARATELY)	1 x Kensington security-cable slot 1 x Kensington nano lock slot

FEATURE TECHNICAL SPECIFICATION

LED INDICATORS	Power Adapter LED Dock Status Indicator RJ45 LEDs
POWER	Power Adapter 130 Watt AC with up to 96 Watt power delivery to any USB-C Notebook
DIMENSIONS	166mm x 76mm x 32mm 6.53in x 2.99in x 1.26in
DOCK WEIGHT (WITHOUT POWER ADAPTER)	416 g (0.92 lb)
OPERATING SYSTEMS	Windows 10 Windows 11 Ubuntu 20.04 and later Mac OS 12.2.1 and later ChromeOS R100 and later
SYSTEMS MANAGEMENT	Wireless vPro supported by the notebook, tablet, or workstation Kernel Direct Memory Access (DMA) protection
DOCKING INTERFACE	Type-C Connector
CABLE LENGTH	0.8 m
MAC ADDRESS	Pass-Through MAC Address
WARRANTY	3-Year Limited Hardware Warranty with Advanced Exchange ² Additional 4- & 5-year warranty optional
MANAGEMENT FEATURES	Wake-On-LAN ³ MAC address pass-through
WHAT'S IN THE BOX	Docking station Power adapter and power cord Documentation (Quick Start Guide, Safety, Environmental, and Regulatory Information)

*HBR (High Bit Rate) is a DisplayPort standard which determines the bandwidth available for displays. Please refer to your notebook's specifications to identify the HBR version.

1 When DisplayLink driver is not installed on the host PC, only 2 video ports are functional simultaneously - HDMI and one of DP (next to HDMI) or USB-C Multi-function DisplayPort

2 Replacement part/unit dispatched, if needed, following completion of phone/online diagnosis. Fee charged for failure to return defective unit. Availability varies.

3 Windows only

Technical specifications subject to change without prior notice. Product availability varies by country. Please contact your Dell representative for more information.

© 2022 Dell Inc. or its subsidiaries. All Rights Reserved. Dell Technologies, Dell, EMC, Dell EMC and other trademarks are trademarks of Dell Inc. or its subsidiaries. Other trademarks may be trademarks of their respective owners. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum.