



# 10 Ft. USB to Serial Converter

# TU-S910 (v3.2R)

- Connect a RS-232 serial device, such as a switch, a modem, to a USB port on your computer
- 10 ft. / 3m cable for easy installation
- Supports USB 1.1, and compatible with USB 2.0 and USB 3.0 ports
- · Supports Windows® and Mac® operating systems

TRENDnet's 10 Ft. USB to Serial Converter Cable, model TU-S910, allows users to conveniently connect an RS-232 serial device, such as a switch, modem or printer, to a USB port on your desktop PC or laptop. The 10 ft. USB to serial adapter supports both Windows® and Mac® operating systems. Integrated cables provide setup flexibility and accommodates most installation scenarios.





USB
ne USB to serial adapter

The USB to serial adapter is compatible with USB 1.1, 2.0 and 3.0 devices.



**RS-232 Serial Connector** 


Connect a RS-232 serial devices, such as switches, modems or printers, to standard USB ports on laptops and desktops.



10 Ft. Flexible Cable

Integrated and flexible 3m (10 ft.) USB cable accommodates most installation scenarios.

# **NETWORKING SOLUTION**





# **FEATURES**



# **Easy Setup**

Simple installation in seconds



### Long & Flexible Cable

Integrated and flexible 3m (10 ft.) USB cable accommodates most installation scenarios



#### **RS-232**

Connect a RS-232 serial devices, such as switches, modems or printers, to standard USB ports on laptops and desktops.



#### USB

The USB to serial adapter is compatible with USB 1.1, 2.0 and 3.0 devices.



## **Operating Systems**

The USB to serial adapter is compatible with Windows® and Mac® operating systems

# **SPECIFICATIONS**

#### **Standards**

• USB 1.1

#### Interface

- 1 x USB Type A
- 1 x RS-232 (9-pin) male
- · Cable length: 3m (10 ft.)

#### **Data Rate**

• Up to 6Mbps

#### Supported OS

- Windows® 11, 10, 8.1, 8, 7
- Mac OS® 10.11, 10.10, 10.9, 10.8, 10.7, 10.6

#### **Operating Temperature**

• 0° - 40° C (32° - 104° F)

### **Operating Humidity**

• Max. 85% non-condensing

#### **Power**

USB powered

#### **Power Consumption**

• 500mA (max.)

#### **Dimensions**

- RS-232 connector: 65 x 35 x 10mm (2.55 x 1.4 x 0.4 in.)
- · Cable length: 3m (10 ft.)

## Weight

• 250g (8.82 oz.)

#### Certifications

- CE
- FCC

#### Warranty

• 2 year

### **Package Contents**

- TU-S910
- · Quick Installation Guide
- CD-ROM (Drivers)

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.