

Portable Stand with Integrated USB-A Hub

 eu.targus.com/products/portable-stand-with-integrated-usb-a-hub-awu100205gl



Model Number: AWU100205GL

Features

- Robust laptop stand with integrated USB hub, foldable to compact size (25.3 x 6 x 1.83 cm), ideal for modern hybrid workers travelling between locations
- Made of high-quality aluminium with high heat reduction. Versatile and universal, supports most laptop devices from 10" - 15.6"
- Expand your laptop USB-C port with one cable to 4x USB-A (3.2 Gen 1) ports
- 4x USB-A support fast 5 Gbps data transfer, perfect for external flash drives
- USB-A ports support max 1.5 A charging for your accessories or smart devices (4 USB-A ports share max 15W)
- USB-C port under the stand offers neat power cable management and supports Power Delivery 3.0 with 100W power pass-through. Share 100W power between laptop devices via USB-C cable and other devices via USB-A and data ports

Overview

Stylish and durable, this Targus® Portable Stand with Integrated USB-A Hub is made with aluminum that is designed to be foldable to an ultra-compact size (25.3 x 6 x 1.83 cm), perfectly stowed within a Targus® backpack or laptop case of the modern mobile worker who's looking to transform their laptop into a workstation at multiple workspaces.

Robust construction with aluminium not only offers a sturdy platform for your laptop, it also has high heat reduction characteristics to help prevent your device from overheating. Plus it can be adjusted to 5 different positions so that your laptop screen stays in your

eye line for the most optimum working posture to reduce back and neck strains.

The Targus® 100W PD GaN Wall Charger (APA109GL) is the perfect companion for this stand with integrated hub, delivering up to 100W power when connected to the USB-C port under the stand, the power then shared between the Laptop via USB-C cable and other accessories connected.

Keep organised whilst working on the go and centrally connect you keyboard, mouse, external flash drive or smart devices via 4x USB-A data ports that all support up to 5 Gbps data transfer rate, ideal for mobile working in multiple locations.

Specifications

- Works With
Windows, Mac, Chrome, Most 10-15.6” Screens
- Colour
Silver
- Connection Technology
USB 3.2 G1
- Host Port Compatibility
USB-C
- Ethernet
No
- Max Host Power
100W
- Output Voltages
Pass-thru
- Power Source
Pass-thru
- HDMI
0
- DisplayPort
0
- Mini Display Port
0
- VGA
0

- DVI-D
0
- DVI-I
0
- Total USB A Ports
4
- USB-C / USB 3.2 G2
1
- Thunderbolt
0
- Audio
0
- Dimensions
26 x 6.2 x 2.7 cm
- Weight
0.36 kg
- Material
Aluminium
- Warranty
Limited 2-Year Warranty
- EAN
5051794036619
- Country of Origin
China