

Lightning Car Charger with Coiled Cable, 1m Coiled Lightning Cable, 12W, White, 2 Port USB Car Charger Adapter for Phones and Tablets, Dual Device In Car iPhone Charger

Product ID: USBLT2PCARW2



Do you carpool to work and need to flip a coin to see who will get to charge their tablet on the way to the office? Do you need to charge your tablet and phone at the same time, so that they're both ready to use by the time you reach your destination?

Whatever your situation, this dual-port car charger offers a high-powered solution for charging two mobile devices simultaneously, while you're on the road.

Charge any Lightning mobile device, including your iPad or iPhone, using this convenient 2 port USB adapter. Reduce tangles and keep your vehicle tidy with the built-in coiled Lightning USB cable.

Along with the Apple device, you can also charge USB-C or Micro-USB mobile devices, such as an Android smartphone, Samsung tablet, or GPS, using an appropriate cable (Lightning cable included. All other cables are sold separately).

Each charge port provides 2.1A of power to assure that you have enough power to charge everything from a phone to a tablet. Whether you're charging two tablets at the same time, or charging a phone and a tablet, you can be sure that all your mobile devices are ready when you needed.

USBLT2PCARW2 is backed for 2-years by StarTech.com, including free 24/5 multi-lingual technical assistance

Certifications, Reports and Compatibility



Applications

Features

- **DUAL DEVICE CAR CHARGER:** Charge two mobile devices simultaneously such as iPhones Pro/Max/Mini/XR up to iPhone 14, iPads, smart phones and tablets; 1m built-in coiled cable provides a tangle free and clean environment in a vehicle
- **HIGH-POWER CHARGING:** The USB car charger provides up to 2.1A for each port allowing the charge of two high-power demanding devices simultaneously; Charge Android devices with the appropriate cable and use the coiled Lightning cable to charge an iPhone
- **DURABLE BUILD:** The portable charger features a flexible coil cable that always returns to the original coiled position even after prolonged use; Built-in latching mechanism that will prevent the charger from slipping out of the cigarette lighter port
- **COMPATIBLE DEVICES:** This in-car USB charger adapter is compatible with iPhones Pro/Max/Mini/XR up to iPhone 14, iPad Air, iPad mini
- **SPECS:** 1m Built-in Cable; Color: White; Cable Type: Coiled; Connectors: USB-A & Lightning; MFI Certified; Performance: 2.1A per port (2.4A, 5V total); Car Phone Charger Cable/Cord; Fits in an automobile auxiliary power outlet

Hardware

| | |
|-----------------------|--------------------------------|
| Warranty | 2 Years |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

Connector(s)

| | |
|-------------|--|
| Connector A | 1 - Automobile Cigarette Lighter (12V AUX) |
| Connector B | 1 - USB 2.0 Type-A (4 pin, 480Mbps) |
| | 1 - Apple Lightning Connector (8-pin) |

Power

| | |
|----------------|------------|
| Input Voltage | 12 ~ 24 DC |
| Input Current | 3 A |
| Output Voltage | 5 DC |
| Output Current | 4.2 A |

Environmental

| | |
|-----------------------|-------------|
| Operating Temperature | 0C to 40C |
| Storage Temperature | -25C to 70C |
| Humidity | 8% to 90% |

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | White |
| Product Length | 3.3 ft [1.0 m] |
| Product Width | 1.4 in [3.5 cm] |
| Product Height | 1.2 in [3.0 cm] |
| Weight of Product | 2.5 oz [70.0 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 5.2 in [13.3 cm] |
| Package Width | 5.1 in [13.0 cm] |
| Package Height | 1.5 in [3.8 cm] |
| Shipping (Package) Weight | 3.7 oz [105.0 g] |

What's in the Box

| | |
|---------------------|---------------------|
| Included in Package | 1 - USB Car Charger |
| | 1 - Product Insert |

**Product appearance and specifications are subject to change without notice.*