

Product Data Sheet

HDMI Splitter 4K





Basic Features

- Duplicates one video input to multiple HDMI outputs.
- Unique EDID Copy function provides maximum definition display compatibility.
- Enable separately learn Audio and Video EDID for multimedia/ home theater system integration.
- Automatic power-save for when signal input is lost.
- Cascaded operation for increased signal outputs.
- Provides crisp clear video images.
- Supports EDID and HDCP, and is Blu-ray ready for high definition display.
- Supports HDMI display resolutions of up to UXGA (1600 x 1200), WUXGA (1920 x 1200), Full HD 1080p (1920 x 1080), UHD (3840 x 2160).
- Includes LED indicators for signal activity monitoring.
- Enables accurate and reliable reproduction of digital video signals without attenuation and distortion.
- Installs in seconds.


Overview

The 1 x 2 or 1 x 4 HDMI Splitter 4K distributes HDMI audio and video out to two or four displays. It supports 4K x 2K resolutions (3840 x 2160 @ 30 Hz). Advanced EDID functionality enables the splitter to read and/or copy EDID information automatically or manually to compatible screens. The splitter can also be daisychained to support additional displays.

Enclosure	Metal
TMDS Clock Rate	300 MHz
Video Resolution (Maximum)	4K x 2K (3840x 2160 @ 30 Hz)
User Controls	(1) EDID Copy button
Connectors	VSP-HDMI1X2-4K: Input: (1) HDMI female, Output: (2) HDMI female; VSP-HDMI1X4-4K: Input: (1) HDMI female, Output: (4) HDMI female;
Indicators	VSP-HDMI1X2-4K: (2) Output Status LEDs; VSP-HDMI1X4-4K: (4) Output Status LEDs;
Power	Consumption: 9–12 VDC, 220 mA
Dimensions	VSP-HDMI1X2-4K: 0.8"H x 6.1"W x 2.6"D (2 x 15.6 x 6.5 cm); VSP-HDMI1X4-4K: 1.6"H x 8.6"W x 5.1"D (4.2 x 21.8 x 13 cm)
Weight	0.627 lb. (0.285 kg)

NOTE: The splitter is not 4K compatible when using Intel® HD 4400 based services.

Connections diagram.



NOTE: The connection diagram for the VSP-HDMI1X4-4K is similar to the VSP-HDMI1X2-4K, except it has four video output ports that can be connected to monitors.

Disclaimer:

Black Box Network Services shall not be liable for damages of any kind, including, but not limited to, punitive, consequential or cost of cover damages, resulting from any errors in the product information or specifications set forth in this document and Black Box Network Services may revise this document at any time without notice.

About Black Box:

Black Box is a leading technology product solutions provider that helps customers build, manage, optimize, and secure their networks. The Black Box quality management system is ISO 9001:2008 certified, and the company has received numerous industry recognitions. Black Box provides its customers with free, 24/7 pre- and post-sales technical support. The Black Box catalog and Web site offer an extensive range of infrastructure products including Cabling, Cabinets & Racks, Data Center Cooling Solutions, Power & Surge Protection, and Environmental Monitoring.

© Copyright 2015. Black Box Corporation. All rights reserved. Black Box® and the Double Diamond logo are registered trademarks of BB Technologies, Inc. Intel is a trademark of Intel Corporation in the U.S. and/or other countries. Any third-party trademarks appearing in this publication are acknowledged to be the property of their respective owners.