



# WD Elements™ SE SSD

## Portable SSD Storage

### Jumpstart Productivity with SSD Speed

- Fast, affordable SSD performance from a brand you can trust
- Up to 400MB/s\*\*
- Up to 2TB\* capacity



Get affordable performance in a pocket-size design for your on-the-go lifestyle. With read speeds up to 400MB/s\*\*, this compact, portable drive lets you accelerate your productivity and move large files fast, no matter where you are. With dependability from a brand you can trust, empower your next-level productivity with a WD Elements™ SE SSD.





# WD Elements™ SE SSD

## Portable SSD Storage

### Product Features

#### Portable SSD Performance

Accelerate your productivity with affordable SSD performance delivered by a brand you can trust.

#### Less Waiting, More Getting Things Done

Read speeds up to 400MB/s\*\* let you move large files fast so you can get more done in your day.

#### Keep Your Most Important Files with You

A compact design and drop resistance up to 2 meters make this the perfect drive no matter where you are.

#### Improve Your Workflow

Whether you're on the job or creating for pleasure, the WD Elements™ SE SSD puts you in control of your content across laptop, desktop and other devices.

#### The Power of Convenience

Seamlessly integrate the drive into your workflow with plug-and-play functionality that's ready to use right out of the box.

#### Get Extra Peace of Mind

The durable and dependable WD Elements™ SE SSD continues the renowned storage legacy of Western Digital and comes backed by a 3-year limited warranty.

## Product Specifications

### CAPACITIES AND MODELS

#### WORLDWIDE

2TB	WDBAYN0020BBK-WESN
1TB	WDBAYN0010BBK-WESN
480GB	WDBAYN4800ABK-WESN

#### JAPAN

2TB	WDBAYN0020BBK-JESN
1TB	WDBAYN0010BBK-JESN
480GB	WDBAYN4800ABK-JESN

### DIMENSIONS

Length:	2.54in (64.51 mm)
Width:	2.54in (64.51 mm)
Height:	0.34in (8.63 mm)
Weight:	0.06lb (1.52 mm)

### OPERATING SPECIFICATIONS

Operating temperature:	0°C to 45°C
Non-op. temperature:	-20°C to 85°C

### CONTENTS

Portable SSD
USB 3.0 Cable
Safety and Warranty Guide

### INTERFACE

USB 3.0 micro B
-----------------

### SYSTEM COMPATIBILITY

Formatted exFAT for compatibility with Windows and MacOS
Reformatting may be required for some operating systems

### LIMITED WARRANTY

3 years Worldwide
-------------------



\*1GB = 1 billion bytes and 1TB = one trillion bytes. Actual user capacity may be less, depending on operating environment.

\*\*Based on read speed. 1 MB/s = 1 million bytes per second. Based on internal testing; performance may vary depending upon host device, usage conditions, drive capacity, and other factors.

Product specifications subject to change without notice. Pictures shown may vary from actual products.

Western Digital, the Western Digital logo and WD Elements are registered trademarks or trademarks of Western Digital Corporation or its affiliates in the US and/or other countries. USB Type-C and USB-C are trademarks of USB Implementers Forum. All other marks are the property of their respective owners.

©2021 Western Digital Corporation or its affiliates. All rights reserved.