

EASY SNIP UTILITY SHEARS

- Strong, stainless steel blades for corrosion resistance
- Textured and molded handles for a secure, comfortable grip
- Spring assist action minimizes hand fatigue
- Wire cutting notch in the lower blade
- Thumb latch secures blades closed during storage
- Ideal for use in the shop, garden, and home



| CATALOG NO. | DESCRIPTION | BARCODE | TOOL LENGTH MM | BLADE LENGTH MM | HANDED | CUTTER HEAD / BLADES | PRODUCT WEIGHT KG | SHELF PACK QTY. | PACKAGING |
|-------------|-------------------------|---------------|----------------|-----------------|--------|------------------------|-------------------|-----------------|-----------|
| WEZSNIPEU | Easy Snip Utility Shear | 4003019299812 | 216 | 100 | Both | Stainless Steel Blades | 0,138 | 6 | Carded |

HEAVY DUTY INDUSTRIAL SHEARS

- Commonly used in cutting fabrics, upholstery, and composite materials
- Precision ground blades provide sharper cutting edges and a longer blade life
- Hot drop-forged nickel-plated blades are strong and durable
- Handle rings designed to comfortably fit users' hands
- Configure the SET-EASY® pivot adjustment to match your preference



| CATALOG NO. | DESCRIPTION | BARCODE | TOOL LENGTH MM | BLADE LENGTH MM | HANDED | HANDLE STYLE | PRODUCT WEIGHT KG | SHELF PACK QTY. | PACKAGING |
|-------------|--|--------------|----------------|-----------------|--------|--------------|-------------------|-----------------|-----------|
| W20 | 10 in Industrial Shear, Bent Handle | 037103240132 | 264 | 121 | Both | Bent | 0,399 | 6 | Carded |
| W20LH | 10 in Industrial Shear, Bent Handle, Left Hand | 037103240187 | 264 | 125 | Left | Bent | 0,399 | 6 | Carded |
| W22N | 12 in Industrial Shear, Bent Handle | 037103240200 | 318 | 150 | Both | Bent | 0,594 | 6 | Carded |

DOUBLE ROUNDED SHEARS

- Precision ground blades for sharper cutting edges and longer blade life
- Hot drop-forged nickel-plated blades are strong and durable
- Blade tips rounded for extra protection
- Handle rings designed to comfortably fit users' hands



| CATALOG NO. | DESCRIPTION | BARCODE | TOOL LENGTH MM | BLADE LENGTH MM | HANDED | PRODUCT WEIGHT KG | SHELF PACK QTY. | PACKAGING |
|-------------|-----------------------------------|--------------|----------------|-----------------|--------|-------------------|-----------------|-----------|
| W20SP | 10 - 3/8 in Double Rounded Shears | 037103240156 | 264 | 125 | Both | 0,399 | 6 | Carded |

HIGH LEVERAGE INDUSTRIAL SHEARS

- Precision ground blades for sharper cutting edges and longer blade life
- Hot drop-forged nickel-plated blades are strong and durable
- Blade tips rounded for extra protection
- Handle rings designed to comfortably fit users' hands
- Red cushion grip handles provide maximum comfort
- SET-EASY® pivot easily and securely adjusts to user preference



| CATALOG NO. | DESCRIPTION | BARCODE | TOOL LENGTH MM | BLADE LENGTH MM | HANDED | PRODUCT WEIGHT KG | SHELF PACK QTY. | PACKAGING |
|-------------|---------------------------------------|--------------|----------------|-----------------|--------|-------------------|-----------------|-----------|
| W1225HLSP | 10 in High Leverage Industrial Shears | 037103240170 | 264 | 125 | Both | 0,399 | 6 | Carded |

HEAVY DUTY CUSHION GRIP INDUSTRIAL SHEARS

- Commonly used in cutting fabrics, upholstery, and composite materials
- Precision ground blades provide sharper cutting edges and a longer blade life
- Hot drop-forged nickel-plated blades are strong and durable
- Red dipped handle rings designed to comfortably fit users' hands
- Configure the SET-EASY® pivot adjustment to match your preference



| CATALOG NO. | DESCRIPTION | BARCODE | TOOL LENGTH MM | BLADE LENGTH MM | HANDED | HANDLE STYLE | PRODUCT WEIGHT KG | SHELF PACK QTY. | PACKAGING |
|-------------|---|--------------|----------------|-----------------|--------|--------------|-------------------|-----------------|-----------|
| W20P | 10 in Industrial Shear, Bent Handle, Cushion Grip | 037103240149 | 264 | 125 | Both | Bent | 0,399 | 6 | Carded |
| W22P | 12 in Industrial Shear, Bent Handle, Cushion Grip | 037103240217 | 318 | 150 | Both | Bent | 0,544 | 6 | Carded |

UPHOLSTERY, CARPET, DRAPERY, AND FABRIC SHEARS

- Ideal for cutting upholstery, carpet, and drapery
- Precision ground blades for sharper cutting edges and longer blade life
- Hot drop-forged nickel-plated blades are strong and durable
- Thick heavy-duty blades for cutting multiple layers and tough materials
- Handle rings designed to comfortably fit users' hands
- SET-EASY® pivot easily and securely adjusts to user preference



| CATALOG NO. | DESCRIPTION | BARCODE | TOOL LENGTH MM | BLADE LENGTH MM | HANDED | PRODUCT WEIGHT KG | SHELF PACK QTY. | PACKAGING |
|-------------|---|--------------|----------------|-----------------|--------|-------------------|-----------------|-----------|
| W20W | 10 in Industrial Shear, Bent Handle, Wide Blade | 037103240194 | 264 | 125 | Both | 0,399 | 6 | Carded |
| W22W | 12 in Industrial Shear, Bent Handle, Wide Blade | 037103240231 | 318 | 150 | Both | 0,635 | 6 | Carded |