

## Completely pre-assembled Signal Towers / eSIGN eSIGN 15 Segments with Siren WH



|                  |                   |
|------------------|-------------------|
| <b>Part No.:</b> | <b>657.800.55</b> |
| <b>Series:</b>   | <b>eSIGN</b>      |



### MECHANICAL DATA

|                             |                                |
|-----------------------------|--------------------------------|
| Height                      | 372 mm                         |
| Diameter                    | 72 mm                          |
| Materials                   | PC                             |
| Dome colour                 | Tranlucent                     |
| Housing colour              | White                          |
| Protection category         | IP66<br>IP69K                  |
| Connection                  | M12 plug 8-pole                |
| Type of fixing              | Base mounting<br>Tube mounting |
| Working temperature minimum | -30°C                          |
| Working temperature maximum | +60°C                          |
| Weight with packaging       | 849 g                          |
| Product weight              | 792 g                          |
| IK-Code (IEC 62262)         | IK08                           |

### ELECTRICAL DATA

|                             |                         |
|-----------------------------|-------------------------|
| Operating voltage           | 24V                     |
| Operating voltage type      | DC                      |
| Operating voltage tolerance | +/- 10%                 |
| Rated operational voltage   | 24 VDC                  |
| Rated operational current   | 620 mA                  |
| Rated inrush current        | 800 mA                  |
| Protection class            | Protection class 3      |
| Pollution degree            | 3                       |
| Overvoltage category        | I                       |
| Isolation voltage           | Ui = 50V / Uimp = 330V  |
| Request to external PSU     | SELV/PELV               |
| connectivity                | Digital entrance<br>USB |

### OPTICAL DATA

|                      |   |
|----------------------|---|
| Light source         | LED   |
| Light colour         | MC >1.000.000 colours                       |
| Optical signal image | Blink<br>Double flash<br>Flash<br>Permanent |
| Blink frequency      | Configurable                                |
| Service life optical | 50,000 h maximum                            |



For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.


Completely pre-assembled Signal Towers / eSIGN  
**eSIGN 15 Segments with Siren WH**

| <b>ACOUSTIC DATA</b>          |                       |
|-------------------------------|-----------------------|
| Volume (max) at 1m distance   | 105 dB                |
| Acoustic signal image         | Multi-tone            |
| Number of tones               | 10 tone               |
| Acoustic service life         | 5,000 h minimum       |
| <b>APPROVAL DATA</b>          |                       |
| Conforms with CE              | Yes                   |
| Conforms with RoHS directive  | Yes                   |
| WEEE                          | Yes                   |
| Conforms with ATEX-directive  | No                    |
| Conforms with CCC-Ex          | No                    |
| Conforms with CCC             | No                    |
| Conforms with UL              | cULus                 |
| UL Type Rating                | Type 4/4X/12/13       |
| Conforms with FCC             | No                    |
| Conforms with IC              | No                    |
| EAC certificate available     | No                    |
| Conforms with UKCA (Importer) | Yes (WERMA (UK) Ltd.) |
| Conforms with CMIM            | No                    |
| Conforms with AS-I            | No                    |
| Conforms with DNV             | No                    |
| Conforms with RoHS CN         | No                    |
| Conforms with VdS             | No                    |
| MTTF-value [years]            | 31                    |

**!** For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.

Completely pre-assembled Signal Towers / eSIGN  
**eSIGN 15 Segments with Siren WH**

**DRAWING**



For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.