Product data sheet Characteristics

ZBZG156

Harmony XB4, Single block for test "light function", 12 and 24 V AC/DC, 24...120 V AC/DC





Main

Harmony XB4 Harmony XB5	
Block for test light	
Integral LED BA 9s	
Single block for test light function	
12 V AC/DC 24 V AC/DC 24120 V AC/DC	
1 wire	
	Harmony XB5 Block for test light Integral LED BA 9s Single block for test light function 12 V AC/DC 24 V AC/DC 24120 V AC/DC

Complementary

Material	Plastic	
Electrical shock protection class	Class I for Harmony XB4 conforming to IEC 60536 Class II for Harmony XB5 conforming to IEC 60536	
Net weight	0.01 Kg	

Environment

Liviloriment		
Ambient air temperature for storage	-4070 °C	
Ambient air temperature for operation	-2570 °C	
Standards	UL 508	
	EN 60947-5-5	
	EN 60947-1	
	EN 60947-5-4	
	IEC 60947-5-1	
	IEC 60947-5-5	
	IEC 60947-5-4	
	CSA C22.2 No 14	
	IEC 60947-1	
	EN 60947-5-1	
	JIS C 4520	
Product certifications	LROS (Lloyds register of shipping)	
	UL listed	
	DNV	
	BV	
	CSA	
	GL	
Vibration resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	30 gn for 18 ms conforming to IEC 60068-2-27	
	50 gn for 11 ms conforming to IEC 60068-2-27	

Packing Units

3	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	18.0 G
Package 1 Height	3.4 Cm
Package 1 width	8.8 Cm
Package 1 Length	5.2 Cm
Unit Type of Package 2	S03
Number of Units in Package 2	165
Package 2 Weight	3.65 Kg
Package 2 Height	30 Cm
Package 2 width	30 Cm
Package 2 Length	40 Cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	☐REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	10 months
vvarranty	18 months

Product Life Status : Commercialised

