

# Wacom®

## Cintiq Pro

### Accuracy redefined in compact design

When creativity strikes, you want to bring your vision to life effortlessly. That's why we've refined Wacom Cintiq Pro 16 to make it even more comfortable and natural to work on. With enhanced ergonomics and an intuitive pen-on-screen experience, you can fully immerse yourself in your craft.



Wacom Cintiq Pro 16  
Featured artist: Superfiction

#### Improved by you

After listening to feedback from our customers, we've enhanced Wacom Cintiq Pro 16 to help boost your creative output.

#### Time-saving ExpressKeys™

Our new physical ExpressKeys™ are now positioned at the rear edge of the display, so there's no compromise on screen size when you're getting to work on your canvas. Designed for more efficient working, the ExpressKeys™ help to give you the time you need to add that extra level of polish to every project.

#### No more unintended touches

To avoid a stray button tap interrupting your workflow, we've refined the display to give you greater control. A new button ensures the touch function only switches on/off when you need it.

#### Connect and play

Linking Wacom Cintiq Pro 16 to your Mac or PC is effortless. All you need to do is connect the USB-C and HDMI cables – whether at your desk or on your lap.

#### Bring a natural precision to every pixel


Our anti-glare 4K screen and Pro Pen 2 work in harmony to create a completely natural pen-on-screen experience. Every stroke you make on the screen's etched glass surface gives you that realistic sensation of pen on paper. And with built in pressure sensitivity, virtually lag-free tracking and superior tilt capabilities, Wacom Pro Pen 2 not only looks like a pen, it feels like one too.

#### Create in comfort

As a creative professional, it pays to be comfortable at your desk. The new VESA mount enables you to mount your device to our optional Adjustable Stand (or other third-party arms) for enhanced stable support of your Wacom Cintiq Pro 16. The cables connect to the top of the screen so there is nothing in your way while creating.



Live. Dare. Create.



Model	Wacom Cintiq Pro 16
Model Number	DTH167
Display Size/Resolution	39.6 cm (15.6 in)/Ultra HD (3840 x 2160)
Active Area	344 x 194 mm (13.6 x 7.6 in)
Size	410 x 266 x 22 mm (16.1 x 10.5 x 0.9 in)
Weight	1.9 kg (4.2 lbs) without optional stand
Color Performance	16.7 million colors (8 bit), 98 % Adobe® RGB coverage (CIE1931) (typ)
Viewing Angle	178° (89/89) H, (89/89) V (typ)
Contrast Ratio/Response Rate	1000:1 (typ)/30 ms (typ)
Power Consumption	Maximum power consumption: 25 W or less, 1.5 W or less when asleep, 0.3 W or less when off
Aspect Ratio/Brightness	16.9/300 cd/m <sup>2</sup> (typ)
Connectivity	1 x USB-C, 1 x HDMI
Graphics Input	USB-C port with DisplayPort Alternate Mode (UHD), or HDMI 2.0 or later (UHD) port and USB-A port
Multi-Touch	Physical switch to turn multi-touch on and off; pan, zoom and rotate gestures available in most applications including Adobe® Photoshop® and Illustrator®
Pen	Battery-free Pro Pen 2 with 2 customisable side switches and 8192 pressure levels in both pen tip and eraser (patented electromagnetic resonance method)
Supported pen tilt angle	+/- 60 degrees
ExpressKeys™	8 easy to access and customizable, application-specific ExpressKeys™ placed at the rear edge of the display
Stand	Integrated pop-out legs for 20° angle; optional detachable Wacom Adjustable Stand with 19° to 85° angle; VESA mount (75 x 75 mm) to attach third party arm or stand
Security	Kensington® MicroSaver 2.0 (lock to be purchased separately)
Productivity Boosters	Physical on/off switch for multi-touch; ExpressKeys™, time-saving on screen settings; Touch Ring on optional ExpressKey™ Remote
Ergonomics	Right or left-handed use; built-in stand (4° without legs or 20° with legs); optional Wacom Adjustable Stand available (19° to 85°)*; VESA mount (75 x 75 mm) to attach third party arm or stand; Wacom Pro Pen 2 with comfortable, ergonomic grip; detachable pen holder to be placed at each side of the display
Compatibility/System Requirements	Windows 7, 8.1, or 10; macOS 10.14 or later; USB-C port with DisplayPort Alternate Mode (UHD), or HDMI 2.0 or later (UHD) port and USB-A port; internet access to download driver
What's Included	Wacom Cintiq Pro, Wacom Pro Pen 2, pen stand with 10 replacement nibs (6 standard, 4 felt) and nib removal tool, detachable pen holder with 3 replacement nibs, PVC-free USB-C to USB-C cable (1.0 m), PVC-free USB-C to USB Standard A cable (1.8 m), PVC-free HDMI 2.0 cable (1.8 m), PVC-free AC adaptor, power cord (1.0 m), quick start guide, cleaning cloth
Additional Accessories	ExpressKey™ Remote, Wacom Adjustable Stand, Wacom Soft Case (Large), Wireless Bluetooth® Keyboard, Wacom Pro Pen 2, Wacom Pro Pen 3D, Wacom Pro Pen slim, replacement nibs, prior generation pens (Pro, Classic, Art, Airbrush, Grip)
Limited Warranty	1 year in Japan & Asia Pacific; 2 years in USA, Canada, Latin America and China; 3 years in Europe, Africa and Middle East with on-site exchange in select regions**

\* Specifications are subject to change. Specification numbers like display size, active area and weight are approximate.

\*\* On-site exchange available in most EU countries (excl. Malta, Cyprus, the Canary Islands or French Overseas Department). More details about terms and conditions at [www.wacom.com/emea-warranty](http://www.wacom.com/emea-warranty).