

DESKTOP DRIVE WITH INTEGRATED USB HUB Data Sheet

Easy backup with integrated USB 3.0 hub to manage and charge your devices

The Seagate[®] Backup Plus Hub drive optimizes external storage with simple file backup for your computers and mobile devices—and an intelligent USB hub to charge and manage your USB-connected devices.

High-speed USB 3.0 and 2.0 connectivity offers plug-and-play functionality on your PC. The drive is formatted for Windows computers. Install the provided NTFS driver for Mac[®] on your Mac computer, and you can use the drive interchangeably between Windows and Mac computers without reformatting.¹

The two front-facing intelligent USB 3.0 ports amplify the functionality of your drive by allowing you to charge and connect two external devices, like your phone, tablet or camera—even if your computer is in off/standby mode.

Back up your favorite files, photos and video from your PC using downloadable Seagate backup software. Run a one-click backup or schedule an automatic backup plan to protect your files in your Backup Plus Hub drive at your convenience.

1 Requires formatting for Time Machine backup.







DESKTOP DRIVE WITH INTEGRATED USB HUB

Specifications								
Retail Packaging	Product Dimensions	Box Dimensions	Master Carton Dimensions	Pallet Dimensions				
Length (in/mm)	4.646 in/118 mm	8.78 in/223 mm	11.299 in/287 mm	40 in/1,016 mm				
Width (in/mm)	1.614 in/41 mm	9.134 in/232 mm	9.173 in/233 mm	47.992 in/1,219 mm				
Depth (in/mm)	7.799 in/198.1 mm	2.756 in/70 mm	9.016 in/229 mm	45.157 in/1,147 mm				
Weight (lb/kg)	2.341 lb/1.062 kg	3.527 lb/1.6 kg	14.947 lb/6.78 kg	996.578 lb/452.04 kg				
Quantities								
Boxes per Master Carton	4							
Master Cartons per Pallet	64							
Pallet Layers	4							

System Requirements

What's Included

Windows® 7 or higher, or Mac OS® X 10.10 or higher operating system^{1,2} •

 SuperSpeed USB 3.0 port (required for USB 3.0 transfer speeds or backwards compatible with USB 2.0 ports at USB 2.0 transfer speeds)^2 $\,$

- Seagate® Backup Plus Hub drive 4-foot (1.2m) USB 3.0 cable
- Seagate backup software³
- . Power adapter
- Quick start guide

NTFS driver for Mac³

Region	Model Number	Capacity	Limited Warranty (years)	EAN Code	Multi-Pack UPC
EMEA	STEL4000200	4 TB	2	763649082782	10763649095468
EMEA	STEL6000200	6 TB	2	0763649081136	10763649093815
EMEA	STEL8000200	8 TB	2	0763649081143	10763649093822
EMEA	STEL10000400	10 TB	2	3660619403240	10763649123987

2 Compatibility may vary depending on use 3 Requires Internet connection.

SEAGATE.COM

AMERICAS Seagate Technology LLC 10200 South De Anza Boulevard, Cupertino, California 95014, United States, 408-658-1000 ASIA/PACIFIC Seagate Singapore International Headquarters Pte. Ltd. 7000 Ang Mo Kio Avenue 5, Singapore 569877, 65-6485-3888 EUROPE, MIDDLE EAST AND AFRICA Seagate Technology SAS 16-18, rue du Dôme, 92100 Boulogne-Billancourt, France, 33 1-4186 10 00

© 2017 Seagate Technology LLC. All rights reserved. Seagate, Seagate Technology and the Spiral logo are trademarks or registered trademarks of Seagate Technology LLC or one of its affiliated companies in the United States and/or other countries. All other trademarks or registered trademarks are the property of their respective owners. When referring to drive capacity, one gigabyte, or GB, equals one billion bytes; and one terabyte, or TB, equals one trillion bytes. Your computer's operating system may use a different standard of measurement and report a lower capacity. In addition, some of the listed capacity is used for formatting and other functions, and thus will not be available for data storage. Complying with all applicable copyright laws is the responsibility of the user. Seagate reserves the right to change, without notice, product offerings or specifications, DS1894.2 1711 EMEA