

Universe	Sport
Type	Lighting
Category	CLASSIC headlamps
Subcategory	CLASSIC headlamps




Hybrid
CONCEPT

ZIPKA®


Simple and ultra-compact, the ZIPKA headlamp offers 200 lumen brightness and a wide beam. Its self-adjusting retractable cord, a Petzl patent, makes it extremely compact, and offers several possibilities for wearing or mounting. With its long burn time, it is practical for outdoor activities like camping or trekking, or for traveling, and also for daily activities and projects around the house. The phosphorescent reflector helps you find it in the dark, and the red lighting prevents members of a group from blinding each other. ZIPKA is a HYBRID headlamp that is also compatible with the CORE rechargeable battery.



Wide, uniform beam for comfortable close-range vision. White and red lighting for nocturnal stealth.



Very compact headlamp.



Exclusive retractable cord system for more wearing options.



ZIPKA is a HYBRID headlamp: it comes with three standard batteries, and is also compatible with the CORE rechargeable battery.

Short Description Simple and ultra-compact headlamp for proximity lighting and some movement. 200 lumens

- Selling Points**
- Ultra-compact format is easy to carry and wear:
 - self-adjusting retractable cord
 - can be worn on the head, the wrist or attached to a tent pole, a seat post...
 - Long burn time
 - Simple to use, thanks to its single button with which to quickly and easily select the lighting mode
 - Three lighting modes: proximity, movement and distance vision
 - Red lighting preserves night vision and stealth, and prevents members of a group from blinding each other
 - Phosphorescent reflector is useful for locating the lamp in the dark
 - ZIPKA is a HYBRID headlamp: it comes with three standard batteries, and is also compatible with the CORE rechargeable battery

-
- Specification**
- Light output: 200 lumens
 - Weight: 66g
 - Beam pattern: wide
 - Energy: Three AAA/LR03 batteries (included) or CORE rechargeable battery (available as accessory)
 - Battery compatibility: rechargeable Ni-MH
 - Certification(s): CE
 - Watertightness: IP X4 (weather resistant)
-

Lighting performance

Lighting color	Lighting modes	Brightness	Distance	Burn time
white	MAX AUTONOMY	5 lm	10 m	240 h
	STANDARD	100 lm	40 m	60 h
	MAX POWER	200 lm	60 m	
red	proximity	2 lm	5 m	100 h
	strobe	visible at 700 m for 400 h		

Specifications by reference

Reference(s)	E93ABA	E93ABB
		
Color(s)	black	red
Made in	MY	MY
Guarantee	5 years	5 years
Packing	1	1
Case quantity	50	50
EAN	3342540106673	3342540106666

Accessory(ies)

CORE
KIT ADAPT
NOCTILIGHT
POCHE