



Standard



Adjusting program (CAL): for quick setting of the balance's accuracy. External adjusting weight required.



Tare: put back displayed value to "0" during weighing process, e.g. to add or remove weighing material from a container.

Order Hotline:
Go to back page of catalogue



STANDARD



STANDARD



KERN CH

LCD display
digit height 11 mm

Data hold function
the weight result can be "frozen" for 5 sec by pressing the HOLD key

Tape measure
extractable,
(length 100 cm)



Hook
stainless steel

Ready for use
Block Battery (9 V) included. AUTO-OFF Function after 3 min without a change of load to preserve the battery

3-pack order example: **KERN CH 15K20 -S3**
6-pack order example: **KERN CH 15K20 -S6**

Model	Read-out d	Weighing range Max	1 piece	3-Pack	6-Pack
KERN	g	kg			
CH 15K20	20	15			
CH 50K50	50	50			
CH 50K100	100	50			
CH 50K500	500	50			

Case WxDxH 90x30x175 mm
(with hook 270 mm). Net weight approx. 250 g.

Convenient
for hanging loads

KERN CH•HCB
Hanging Scales

KERN HCB

Snap link
stainless steel with safety catch opening 15 mm. Can be reordered at any time, **KERN HCB-A01**

Adjustment program CAL
External test weights available at an additional price

LCD display
digit height 12 mm

Data hold function
the weight result can be "frozen" for 5 sec by pressing the HOLD key

Ready for use
Battery size AA (3x 1,5 V) included. Operating time approx. 300 h. AUTO-OFF Function after 3 min without a change of load to preserve the battery

S-hook
stainless steel. Opening approx. 25 mm. Can be reordered at any time, **HCB-A02**

Price reduction

3-pack order example: **KERN HCB 20K50 -S3**

Model	Read-out d	Weighing range Max	1 piece	3-Pack	OPTION DKD Certificate KERN
KERN	g	kg			
HCB 20K50	50	20			963-128
HCB 50K100	100	50			963-128
HCB 100K200	200	100			963-129
HCB 200K500	500	200			963-129
Feinanzeige					
HCB 20K10	10	20			963-128
HCB 50K20	20	50			963-128
HCB 99K50	50	99			963-129
HCB 200K100	100	200			963-129

Case WxDxH 80x45x150 mm. Net weight approx. 400 g.
Total height with snap link and S-Hook 290 mm.

65

KERN - Your DKD-Calibration Partner

issues DKD calibration certificates for balances and test weights in its own accredited laboratories. It is internationally valid.

KERN is a manufacturer of test weights in the international classes of accuracy **E1, E2, F1, F2, M1, M2, M3, from 1 mg up to 2000 kg**
DKD = German Calibration Service



Your KERN specialist dealer