

## 5-Port 10/100/1000Mbps Desktop Switch

### TL-SG105

#### ⦿ Features:

- Up to 2000Mbps full duplex bandwidth for high-speed data processing
- 5 10/100/1000Mbps Ethernet ports
- Innovative energy-efficient technology saves up to 65% of power consumption
- Plug and play design simplifies installation
- Advanced QoS feature guarantees the requirements of different bandwidth applications
- IEEE 802.3x flow control provides reliable data transfer
- Auto-MDI/MDIX eliminates the need for crossover cables
- Auto-Negotiation ports provide smart integration between 10Mbps, 100Mbps and 1000Mbps hardware



#### ⦿ Description:


The TL-SG105 5-Port 10/100/1000Mbps desktop switch provides an easy way to expand your wired network. All 5 ports support Auto-MDI/MDIX, eliminating the need to worry about the type of cable to use. Featuring full duplex mode, the TL-SG105 can process data at a rate of up to 2000Mbps making it an ideal choice for expanding your high performance wired network. Moreover, with innovative energy-efficient technology, the TL-SG105 can save up to 65% of power consumption, making it an eco-friendly solution for your home or office network.

## ⦿ Specifications:

Interface	5 10/100/1000Mbps, Auto-Negotiation, Auto-MDI/MDIX Ports
IEEE Standards	IEEE 802.3, IEEE 802.3u, IEEE802.3ab, IEEE 802.3x
Protocol	CSMA/CD
Switching Features	Half and Full Duplex, MAC Address Learning, 10.0Gbps backplane bandwidth
Forwarding Rates	10BASE-T: 14880pps/port; 100BASE-TX: 148800pps/port 1000BASE-T: 1488000pps/port
Advanced Features	IGMP Snooping IEEE 802.1P QoS
LEDs	Power, Ethernet Ports(1, 2, 3, 4, 5)
Energy Saving	65%
Power Supply	9V 0.6A
Certifications	CE, FCC, RoHS
Dimensions (W x D x H)	3.9 x 3.9 x 1.0 in. (99.8 x 98 x 25 mm)
Environment	Operating Temperature: 0°C~40°C (32°F~104°F) Storage Temperature: -40°C~70°C (-40°F~158°F) Operating Humidity: 10% ~ 90% non-condensing Storage Humidity: 5%~90% non-condensing

## ⦿ Diagram:

### TYPICAL NETWORK SETUP



### Package:

- 5-Port 10/100/1000Mbps Desktop Switch TL-SG105
- User Guide
- Power Adapter

### Related Products:

- 150Mbps Wireless N ADSL2+ Modem Router TD-W8951ND