

Expert Power Control 8212 / 8213



Expert Power Control 8213
Power Ports on front panel



Expert Power Control 8212
Power Ports on rear panel

Features

- 4 Power Ports individually switchable directly on the device, via HTTP, command line tool and RS232 serial interface
- Status and Power-up delay (0...9999 seconds) adjustable individually for each Power Port after power blackout
- Simultaneous power-up of multiple Power Ports prevented by latency time of 1 second
- Programmable turn-on/turn-off sequence
- 4-channel watchdog, an individual watchdog (ICMP/TCP) can be assigned for each Power Port
- Clearly visible LED display for total current (actual, peak), IP address, sensor data and error reports
- Firmware update via Ethernet during operation
- HTTP 1.1, e-mail, DHCP, SNMPv1 (Traps), SNMPv2c (Traps), Syslog
- Access control via IP Access Control List
- Access control via optional HTTP password
- Free Android and iOS app allows access from anywhere

- Low internal power consumption, max. 5 W
- Developed and manufactured in Germany

Electrical Connections

- 1 power supply (IEC C20, max. 16 A)
- 4 Power Ports (IEC C13, max. 10 A)
- Ethernet connector RJ45 (10/100 Mbit/s)
- 2 mini-DIN connectors for optional sensors or serial interface

Technical Details

- Dimensions: 19 inch, 1 rack unit
- Weight: ca. 2.2 kg
- Operating temperature: 0-50 °C (non-condensing environment)

Ordering Information

Order code	Product	Feature	Operating Voltage	Maximum Current
8212	Expert Power Control 8212	Power connectors on rear panel	230 V	16 A
8213	Expert Power Control 8213	Power connectors on front panel	230 V	16 A
7001	Temperature Sensor 7001	-20°C to +80°C		
7002	Hybrid Sensor 7002	-20°C to +80°C / 0-90% humidity		
7990	RS232 Adapter Cable 7990			



Gude Analog- und Digitalsysteme GmbH
Eintrachtstr. 113
50668 Koeln, Germany

T +49.221.912 90 97
F +49.221.912 90 98

mail@gude.info
www.gude.info

