

# WTCP 51 - Soldering Station Set

Order No.:0053220699



## Soldering Station Magnastat 50 W, 230 V

The Weller Magnastat system operates through a ferro-magnetic device which changes ist characteristics when specific temperatures are reached. This causes it to either attract or repel a permanent magnet which operates a power supply switch. In this way power to the heating element can be quickly switched on or off to either provide extra power for soldering operations or reduced power when idling. Various preselected tip temperatures (260°C, 310°C, 370°C, 425°C, 480°C) are available for different soldering tasks. The unit is not suitable for ESD application because the iron is not antistatic.

#### **Top Attributes**

- On / Off controller
- Temperature control variable by soldering tip exchange
- Protection class 1
- Antistatic housing
- Hard grounded
- Dimensions: 166 x 115 x 101 mm (L x W x H)

## **Technical Data**

| Equipotential Bonding/ hard grounding explanation | Normal state |
|---|--------------|
| Temperatur control comment                        | Magnetic     |
| Display included & Size                           | No display   |
| ESD safe  | Yes          |
| Equipotential Bonding/ hard grounding             | Yes          |
| Display backlight                                 | No           |
| Antistatic housing                                | Yes          |
| Temperature stability                             | 5 °C         |
| Power unit wattage                                | 50 W         |
| Mains supply Voltage                              | 230 V        |
|   |              |

**Cooper Tools GmbH** Carl-Benz-Str. 2 74354 Besigheim Germany Phone: +49 (0) 7143-580-0 Fax: +49 (0) 7143-580-108 cht-germany@cooperindustries.com www.coopertools.eu





| Power supply frequency                    | 50 Hz        |
|---|--------------|
| Output voltage                            | 24 V         |
| Protection class Soldering iron           | 3            |
| Protection class Control/ Power unit      | 1            |
| Number of tools controlled simultaneously | 1            |
| Temperature accuracy                      | 9 °C         |
| Temperature regulation                    | 260 - 480 °C |

# **Packaging information**

Shelf pack size (Units per shelf pack)

1

**Cooper Tools GmbH** Carl-Benz-Str. 2 74354 Besigheim Germany Phone: +49 (0) 7143-580-0 Fax: +49 (0) 7143-580-108 cht-germany@cooperindustries.com www.coopertools.eu

