
Data sheet

Article Description

Article Picture

Line-intermediate Switch Type 5055

3 (2) A, 250 V~, 1-pole, on-off-switch


catch locking housing,
strain relief by insulant screws,

- for cables H03VV-F 2 x 0,50 mm² or 2 x 0,75 mm²
- degree of protection IP40
- screw terminals (Suitability for terminals for connecting unprepared conductors)
- LWH 67 x 22 x 17 mm



Suitable for LED!!!

Height with rocker: 17 mm
 Height without rocker: 15 mm
 Diameter rocker: 15 mm



<i>inter BÄR-item</i>	<i>Colour housing</i>	<i>rocker</i>
5055-004.01	black	black
5055-008.01	white	white
5055-009.01	brown	brown
5055-010.01	gold	gold
5055-020.01	titan	black

Technical modifications reserved!
Works at 230 V-mains must only be carried out by a specialist!