Hirschmann Automation and Control GmbH






GML 209 NJ LED 24 HH grau/grey

Industrial Connectors:Rectangular connectors GDM-series:Type B Industrial standard:Cable socket with electronic insert

Product description	
Description	function indicator (LED) with protective circuit (diode)
Туре	GML 209 NJ LED 24 HH grau/grey
Order No.	933 389-106
Other standard types	transparent housing, locking screw black: Order No. 933 389-100
Number of contacts	2 + PE
Cable gland	PG 9 (grey)
Conductor size	max. 1.5 mm ²
Standard	industrial standard (11 mm)
Housing Color	transparent
Construction type	В
Description of Wiring	
LED color	LED red
Suppressor	diode
Other characteristics	correct polarity must be ensured
Drawing	



Technical data	
Pin dimensions	6.3 mm x 0.8 mm
Rated voltage	DC 24 V
Rated current	8 A
Contact resistance	<= 4 mOhm
Type of termination	screw / cable shoe / cable eye
Suitable cables	4.5 mm to 7 mm diameter
Mounting	central screw
Material	
Contact surface material	Sn
Contact bearer material	PA

Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 65
Pollution severity	3
Temperature range	-40 °C to +90 °C
Inflammability class	
Housing	94 V-1
Contact bearer	94 HB
Approvals	
UR	UR
VDE	VDE
Packing unit	
Packaging unit	50 pieces
Scope of delivery and accessories	
Accessories to order separately	(NBR) flat gasket GM 207-3, Order No. 731 423-002; knurled screw GDM 3011-8, Order No. 732 574-001; stainless steel screw GDM 3011 RF-1, Order No. 734 363-001