


**Dekafix  
DEK 6 FWZ 1-10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



The dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a large range of ready-printed markers. Strips for fast installation in one work step. The printing is easy to read, rich in contrast, and is available in five widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Connector markers, suitable for all Weidmüller cable connectors
- Available as blank cards, MultiCard or as cards with standard printing

**General ordering data**

|            |  |
|------------|--|
| Type       | DEK 6 FWZ 1-10   |
| Order No.  | <a href="#">0518960001</a>   |
| Version    | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, White |
| GTIN (EAN) | 4008190014261  |
| Qty.       | 500 pc(s).   |

**Data sheet**

**Dekafix  
DEK 6 FWZ 1-10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

|            |        |       |      |
|------------|--------|-------|------|
| Length     | 5 mm   | Width | 6 mm |
| Net weight | 0.05 g |       |      |

**General data**

|                                   |              |  |         |
|-----------------------------------|--------------|--|---------|
| Application/manufacture           | Weidmueller  | Colour                                       | White   |
| Colour of printing                | Black        | Length                                       | 5 mm    |
| Material                          | Polyamide 66 | Material colour according to resistance code | 9       |
| Operating temperature range, max. | 100 °C       | Operating temperature range, min.            | -40 °C  |
| Orientation of print              | horizontal   | Printed characters                           | Numbers |
| Printing method                   | MC Laser     | UL 94 flammability rating                    | V-2     |
| Width                             | 6 mm         |  |         |

**Connector markers**

|                 |      |
|-----------------|------|
| Pitch in mm (P) | 6 mm |
|-----------------|------|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000761    | ETIM 4.0   | EC000761    |
| ETIM 5.0   | EC000761    | ETIM 6.0   | EC000761    |
| UNSPSC     | 30-21-18-07 | eClass 5.1 | 27-14-11-37 |
| eClass 6.2 | 27-14-11-37 | eClass 7.1 | 27-14-11-37 |

**Approvals**

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|