

Product Information

2470PJO100P30

EAN 4031582010411

Swivel castor, Housing made of pressed steel, zinc-chromatised, double ball bearing swivel head, wheel axle with nut.

Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing, bolt hole

Castors can be mounted with standard screws; various length screws can be used..

Option:

This castor is also in electric conductive version available. Please replace PJO with YGO when ordering..

Wheel diameter	100 mm
Width of Tread	32 mm
Centre hole	11 mm
Offset	38 mm
Swivel Interference	176 mm
Overall height	135 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.552 Kg / daN
Dynamic Load capacity	80 Kg / daN
Static Load capacity	160 Kg / daN
Swivel Radius	88 mm



Versions:

