## 6000 Series Buccaneer



6000 Series Buccaneer – circular connectors that combine the ease of use of a push/pull coupling mechanism with proven environmental sealing. Available with metal or plastic bodies, the range supports both data (USB and Ethernet), signal and mains power. Designed and independently tested to IP66, IP68 & IP69K standards, they are ideal for applications where ingress of dust and water must be avoided and where ease of connection, space and appearance are important considerations.

- O Push/Pull mechanism
  Secure, quick connector mating and release
- 30° twist locking Tamperproof lock prevents accidental un-mating
- IP66, IP68 and IP69K when mated
   Suitable for a wide range of dust and water borne environments
- All plastic body version; UL94-V0 rated, UV stable, halogen free Light-weight, self-extinguishing material suitable for long-term outdoor use
- Flex, flex in-line & panel mount body styles, with sealing caps
   Complete family of products maintain sealing integrity in all styles
- O Polarisation and visual alignment features Aids the correct mating of connectors
- 2 to 22 poles up to 16A, 277V rated
   Suitable for mains power to signal applications
- 'Scoop proof' contacts
   Prevents damage through mis-mating ideal for 'blind mating' applications
- cULus, UL, VDE Internationally recognised certification
- O Screw, Crimp and Solder terminations available






Flex Cable Connector



- O Mates with In-Line Flex or Panel Mounting versions PXP6011 & PXP6012
- O Push/pull locking ring with 30° twist locking
- Pin or socket versions
- Leading earth on 3 pole connectors
   2, 3, 8, 16 & 22 pole
- O Screw, solder and crimp termination




Poles	Termination	Pin Contacts	<b>Socket Contacts</b>	Contacts
2	Screw	PXP6010/02P/ST	PXP6010/02S/ST	Supplied Fitted
2	Crimp / Solder	PXP6010/02P/CR	PXP6010/02S/CR	Contacts Required
3	Screw	PXP6010/03P/ST	PXP6010/03S/ST	Supplied Fitted
3	Crimp / Solder	PXP6010/03P/CR	PXP6010/03S/CR	Contacts Required
8	Crimp / Solder	PXP6010/08P/CR	PXP6010/08S/CR	Contacts Required
16	Crimp / Solder	PXP6010/16P/CR	PXP6010/16S/CR	Contacts Required
22	Crimp / Solder	PXP6010/22P/CR	PXP6010/22S/CR	Contacts Required

In-line Flex Cable Connector



- Mates with Flex Cable connector PXP6010
- For in-line cable connection
- Pin or socket versions
- Leading earth on 3 pole connectors
- O 2, 3, 8, 16 and 22 pole
- O Screw, solder and crimp termination



	20	0-	
ヒメト	70	U	


PXP6010

Poles	Termination	Pin Contacts	<b>Socket Contacts</b>	Contacts
2	Screw	PXP6011/02P/ST	PXP6011/02S/ST	Supplied Fitted
2	Crimp / Solder	PXP6011/02P/CR	PXP6011/02S/CR	Contacts Required
3	Screw	PXP6011/03P/ST	PXP6011/03S/ST	Supplied Fitted
3	Crimp / Solder	PXP6011/03P/CR	PXP6011/03S/CR	Contacts Required
8	Crimp / Solder	PXP6011/08P/CR	PXP6011/08S/CR	Contacts Required
16	Crimp / Solder	PXP6011/16P/CR	PXP6011/16S/CR	Contacts Required
22	Crimp / Solder	PXP6011/22P/CR	PXP6011/22S/CR	Contacts Required

Front Panel Mounting Connector



- O Mates with Flex Cable connectors PXP6010
- Front panel mounting
- Single hole fixing
- Pin or socket versions
- Leading earth on 3 pole connectors
- 2, 3, 8, 16 and 22 pole
- O Screw, solder and crimp termination



$\neg \lor \Box$	20	40
	00	12

Poles	Termination	Pin Contacts	<b>Socket Contacts</b>	Contacts
2	Screw	PXP6012/02P/ST	PXP6012/02S/ST	Supplied Fitted
2	Crimp / Solder	PXP6012/02P/CR	PXP6012/02S/CR	Contacts Required
3	Screw	PXP6012/03P/ST	PXP6012/03S/ST	Supplied Fitted
3	Crimp / Solder	PXP6012/03P/CR	PXP6012/03S/CR	Contacts Required
8	Crimp / Solder	PXP6012/08P/CR	PXP6012/08S/CR	Contacts Required
16	Crimp / Solder	PXP6012/16P/CR	PXP6012/16S/CR	Contacts Required
22	Crimp / Solder	PXP6012/22P/CR	PXP6012/22S/CR	Contacts Required

### BUCCANEER FOR POWER

## 6000 Series Buccaneer

Metal Version




Flex Cable Connector



- Mates with In-Line Flex or Panel Mounting versions PXM6011 and PXM6012
- Push/pull locking ring with 30° twist locking
- Pin or socket versions
- Leading earth on 3 pole connectors
- 2, 3, 8, 16 and 22 pole
- Screw, solder and crimp termination
- Cable braid termination accessory option, add /SNsuffix






Poles	Termination	Pin Contacts	<b>Socket Contacts</b>	Contacts
2	Screw	PXM6010/02P/ST	PXM6010/02S/ST	Supplied Fitted
2	Crimp / Solder	PXM6010/02P/CR	PXM6010/02S/CR	Contacts Required
3	Screw	PXM6010/03P/ST	PXM6010/03S/ST	Supplied Fitted
3	Crimp / Solder	PXM6010/03P/CR	PXM6010/03S/CR	Contacts Required
8	Crimp / Solder	PXM6010/08P/CR	PXM6010/08S/CR	Contacts Required
16	Crimp / Solder	PXM6010/16P/CR	PXM6010/16S/CR	Contacts Required
22	Crimp / Solder	PXM6010/22P/CR	PXM6010/22S/CR	Contacts Required

In-line Flex Cable Connector



PXM6011

- Mates with Flex Cable connector PXM6010
- For in-line cable connection
- Pin or socket versions
- Leading earth on 3 pole connectors
- O 2, 3, 8, 16 and 22 pole
- O Screw, solder and crimp termination
- Cable braid termination accessory option, add /SNsuffix




Poles	<b>Termination</b>	Pin Contacts	<b>Socket Contacts</b>	Contacts
2	Screw	PXM6011/02P/ST	PXM6011/02S/ST	Supplied Fitted
2	Crimp / Solder	PXM6011/02P/CR	PXM6011/02S/CR	Contacts Required
3	Screw	PXM6011/03P/ST	PXM6011/03S/ST	Supplied Fitted
3	Crimp / Solder	PXM6011/03P/CR	PXM6011/03S/CR	Contacts Required
8	Crimp / Solder	PXM6011/08P/CR	PXM6011/08S/CR	Contacts Required
16	Crimp / Solder	PXM6011/16P/CR	PXM6011/16S/CR	Contacts Required
22	Crimp / Solder	PXM6011/22P/CR	PXM6011/22S/CR	Contacts Required

Front Panel Mounting Connector



- Mates with Flex Cable connectors PXM6010
- Front panel mounting
- Single hole fixing
- Pin or socket versions
- Leading earth on 3 pole connectors
- 2, 3, 8, 16 and 22 pole
- Screw, solder and crimp termination



PXM6012
---------

Poles	Termination	Pin Contacts	<b>Socket Contacts</b>	Contacts
2	Screw	PXM6012/02P/ST	PXM6012/02S/ST	Supplied Fitted
2	Crimp / Solder	PXM6012/02P/CR	PXM6012/02S/CR	Contacts Required
3	Screw	PXM6012/03P/ST	PXM6012/03S/ST	Supplied Fitted
3	Crimp / Solder	PXM6012/03P/CR	PXM6012/03S/CR	Contacts Required
8	Crimp / Solder	PXM6012/08P/CR	PXM6012/08S/CR	Contacts Required
16	Crimp / Solder	PXM6012/16P/CR	PXM6012/16S/CR	Contacts Required
22	Crimp / Solder	PXM6012/22P/CR	PXM6012/22S/CR	Contacts Required



O '	/ 0 - 1 - 1 -	0 1 1 -
Urimb.	/ Solde	r Contacts



Gold Plated Current ratings: 2 & 3 pole : 16A 8 pole : 10A 16 pole : 3A 22 pole : 2A

Contacts (for 2 & 3 pole) (Supplied in packs of 10)	Crimp	Solder
Pins	SA3545/P	SA3624/P
Sockets	SA3545/S	SA3624/S
Contacts (for 8 pole) (Supplied in packs of 10)	Crimp	Solder
Pins	SA3544/P	SA3623/P
Sockets	SA3544/S	SA3623/S
Contacts (for 16 & 22 pole) (Supplied in packs of 10)	Crimp	Solder
Pins	SA3542/P	SA3622/P
Sockets	SA3542/S	SA3622/S

Crimp Tooling

Extraction Tool



and 22 pole crimp contacts

Crimp Tools for 2, 3, 8, 16

### **Crimp Tooling**

Crimp Tool (2 & 3 pole) PNo.14232 PNo.14232/2/SP Positioner (2 & 3 pole) Crimp Tool (8, 16 & 22 pole) PNo.14025 Positioner (8 pole)
Positioner (16 & 22 pole) PNo.15021/SP PNo.15019/SP



Extraction Tool for 2, 3, 8, 16 and 22 pole contacts

For removal of all contact

carriers

### Extraction Tools

Extraction Tool PNo.14946/SP (2 & 3 pole) Extraction Tool PNo.14945/SP (8 pole) Extraction Tool PNo.14944/SP (16 & 22 pole)

Contact Carrier Removal Tool




Tools

Contact carrier removal tool PNo. 14917/SP (all poles)





- Maintains IP Rating of Unmated Connectors  $\bigcirc$
- PXM6081: Fits PXM6010 (Flex Connector) PXM6082: Fits PXM6011
- (Flex In-Line Connector) PXM6083: Fits PXM6012 (Panel Connector)



Cable Gland Pack



PXP6088

Pack of all cable glands to suit cable ranges from 4.0 to 10.0mm diameter

Cable Braid Termination Option



PXM6090

For cable braid termination Supplied with ty-rap



PXX	6XXX	/ <b>xx</b>	X	/ <b>xx</b> /	/ xxxx	/ <b>xx</b>
Series Designation PXM= Metal Series PXP= Plastic Series	Series / Body Style Body Styles 6010 = Flex 6011 = Flex In-Line 6012 = Panel	No. of Contacts  No. of Contacts  02 = 2 Pole 03 = 3 Pole 08 = 8 Pole 16 = 16 Pole 22 = 22 Pole	Contacts Type Contacts Type P = Pin S = Socket	Terminations Contacts Termination CR = Contacts Required ST = Screw (2 and 3 pole only)	Cable Entry Size Cable Entry Size (for Flex and Flex In- Line connectors only)  0405 = 4-5mm (Dark Grey)  0507 = 5-7mm (White)  0709 = 7-9mm (Yellow)  0910 = 9-10mm (Light Grey)	Cable Brand Termination Accessory Cable Braid Termination Accessory (for Flex and Flex In-Line connectors only) SN if required Blank if not required

### Examples

PXM6010/03P/CR/0507= Flex cable connector, 3 pole, pin contacts with 5 to 7mm cable glands PXM6012/03/S/ST= Front panel mounting connector, 3 pole, socket with screw termination





Electrical:						Mechanical:	
No. Poles:	2	3	8	16	22	Locking mechanism	Push/pull with 30° locking Patent applied for
Current Rating: See de-rating curves for further information						Sealing:	IP66 to En60529:1992+A2:2013 IP68 to En60529:1992+A2:2013 (10m depth
VDE	16A	16A	10A	ЗА	2A		for 2 weeks)
UL	16A	16A	7A	ЗА	3A		IP69k to DIN 40050-9
cUL	11A	11A	4A	1.5A	1.5A		
CCC Voltage	277V	277V	277V	60V	60V	Salt Mist (plastic) :	EN60068-2-52 Test Kb Salt Mist (Cyclic) Marine Severity Level 1
Rated cable	18 AWG	18 AWG	18 AWG	22 AWG	26 AWG	Salt Mist (metal):	EN60068-2-11 Test Ka Salt Mist
	AWG	Avva	AVVG	AVV	AWG	Contact Accommodation:	
Contact Resistance:	<10mΩ	2				2 & 3 pole crimp / solder	14 to 18AWG
Insulation Resistance:	$>10^{6}M_{\odot}$	Ω @500	V dc			2 & 3 pole screw terminals	1.5mm <sup>2</sup> max
AC Breakdown voltage:						8 pole crimp / solder	18 to 20AWG
2 pole	>10kV					16 pole crimp / solder	22 to 26AWG
3 pole	>8kV					22 pole crimp / solder	22 to 26AWG
8 to 22 pole	>5kV					0-61- 4	4.40
Operating Temp. Range:	_40°C 1	to +120°	°C			Cable Acceptance:	4-10mm dia.
operating rempersional	40 0	10 1120	0			Cable retention force	
Approvals:						(to BS EN61984):	
<b>RL</b> UL (E214972)	UL1977	7				4 - 9mm dia cable	80N
c <b>Al</b> us cULus (E214972)		No.182.3		87 (R200	9)	9 - 10mm dia cable	100N
CCC (Pending)						Terminations:	
						2 Pole:	Screw Terminals
						3 Pole:	Screw, crimp or solder terminals
						8 Pole:	Crimp / Solder Contacts
						16 Pole:	Crimp / Solder Contacts
						22 Pole:	Crimp / Solder Contacts
						Tightening Torques:	
						Gland Nut:	1.13Nm (10lb.in)
						Panel Nut:	1.7Nm (15lbf.in.)
						Panel Nut Thread:	M22 x 1.5-6g
						Dimensions:	00
						Diameter: (over coupling ring)	32mm 22.5mm
						Diameter: (panel hole cut-out)	22.JIIIII

Materials:	Plastic	Metal
Body:	PC/ PBT	Brass
Colour:	Grey	Matt silver
Contacts:	Brass, Nickel Plate (Screw and Crimp) Brass, (3A – Gold plated)	Brass, Nickel Plate (Screw and Crimp) Brass, (3A – Gold plated)
O Rings & Gaskets:	Silicone	Silicone
Flammability Rating:	UL94 V-0	-
Halogen free	Yes	-
UV Resistance:	ISO 4892 part 3 cycle 1 (QUV)	-
RoHS	Compliant	Compliant

### BUCCANEER FOR POWER

## 6000 Series Buccaneer



The thermal properties of the materials used in the construction of a connector limit the current carrying capacity. There are a number of factors that determine the amount of current that can be handled: contact spacing, size of cable, ambient temperature and the heat that is generated by the current passing through the connector.

The maximum current varies with different contact layouts, and because of these factors it is necessary to produce de-rating curves for each pole variant. This de-rating curve is specified in the standard IEC 60512 part 3. De-rating curves are plotted for each contact carrier combination with the current being carried simultaneously by all contacts. These graphs show the heat rise generated as the current is increased.

The red line indicates the direct correlation between current applied and the measured temperature rise within the connector. The dotted blue line shows rated current and the green line is derived by applying a factor of 0.8 to the original plot data to give a de-rating curve. The dashed blue line shows the rated current.

The shaded area under the 0.8 curve shows the permitted operating area, and allows safe current vs ambient temperature characteristics to be determined.

