## HIGH CURRENT SWITCHING MODE DC regulated power supply

Manson



SPS - 8250 , SPS - 9250

## **Description**

The series of HIGH POWER SWITCHING MODE DC REGULATED POWER SUPPLIES provide high current 25 Amps output in a lightweight and compact size case. They are suitable for a wide range of uses, such as radio equipment, and are ideal for high power car stereo work. In addition to variable output from 3 to 15VDC, a fixed 13.8VDC can be selected. Overload, Over temperature, and Over voltage protection are standard.

## **Features**

- 25A current output
- High efficiency
- Adjustable output voltages 3V to 15V
- Fixed voltage mode at 13.8V
- Light weight and small size
- Overload temperature protection
- Current fold-back circuit with LED indicator prevents overloading
- Over voltage protection at 16.5V
- Variable speed thermally controlled fan.
- High RFI stability
- Power factor correction >0.95
- Housing are available in (Pantone warm grey 1C
  - or Pantone dark grey 433C \(\bigsim\)



**SPS** - 8250





## **SPECIFICATIONS**

Variable Output Voltage
Fixed Output Voltage Mode
Rated Output Current
Ripple and Noise (P-P)
Load Regulation
Line Regulation

Input Voltage

Efficiency

Meter Type V meter Range

A meter Range

Meter's Accuracy

**Cooling System** 

**Protection Devices** 

**Approvals** 

Dimension (WxHxD)

Weight

Remarks

**SPS-8250** 

SPS - 9250

010 0200	313 7250
3 - 15V DC	
13.8V DC	
25A	
50mV	
200mV	
50mV	
230VAC / 50Hz	
> 78%	
Analog Meter	LED Meter
0 - 20V	3 digit display
0 - 30A	3 digit display
7% fsd	1% + 2 digit
Variable speed thermally control fan	
Overload, Short circuit, Over Temperature, OVP	
CE EN60950, EN55022	
220 x 110 x 220 (mm)	
2.7 KG	
Power factor correction >0.95 at optimal load	

\* SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE \*