

**Sub**

**product**

Keyswitch Lock

ø12

ø16

ø19

Cam Lock

Furniture Lock

Cable Lock

Pad Lock/Travel Lock

Zinc/Aluminum die casting

Metal Stamping

Plastic Injection

Molding Development

Lock Parts


**product**

product > Keyswitch Lock > ø19



Add to Inquiry Cart

[View More Details](#)



**No.:** S246 S246M

**Product Name:** KEYLOCK SWITCH

**DESCRIPTION:**

- Zinc alloy die cast housing and cylinder.
- Bright chrome plated standard.
- Stainless steel capped bezel with dust shutter mechanism.
- 5 disc tumbler mechanism.
- Reversible double-bitted brass keys, nickel plated.
- Key may be withdrawn in one or both positions.
- Silver plated contacts and terminals.
- S246 2 position (off-on) 2 terminals.
- S246M 2 position (off-on) 2 terminals, spring loaded for momentary contact.
- Hex nut mounted.
- All keyed alike or 25 combinations standard.
- 100 combinations available.

**SPECIFICATIONS:**

- Contact Rating: 4A 125VAC, 2A 250VAC
- Contact Resistance: 10 Milli-Ohms Max.
- Insulation Resistance: 500 Meg-Ohms Min. (500VDC)
- Dielectric Strength: 1500 VAC - 1 Minute.

**KEY-PULL FIGURES :**

- -Off Position
- ◐ -Indicates Key-Pull
- -Indicates No Key-Pull




Fig. No.	Lock Number	Pole	Positions	Terminals	Key Pulls	Turn			Type
1	S246-1	1	2	2	1	90 °	Off	On	SPST
2	S246-2	1	2	2	2	90 °	Off	On	SPST
1	S246M	1	2	2	1	90 °	Off	On	SPST

\*( ) : Momentary Contact

Unit: mm

HOLE SIZE

