

KNIPEX Quality - Made in Germany



# KNIPEX Crimp Assortments in TANOS MINI-systainers



- sturdy construction
- secure transport
- stackable



# New KNIPEX Crimp Assortments, in TANOS MINI-systainers



97 90 21



97 90 22



97 90 23



97 90 24

► In a TANOS MINI-systainer® (solid plastic box)

► two stackable plastic inserts with 6 trays each for connectors

## Contents of the new assortments

Article-No.	EAN-Code	Pliers	Connectors	
	4003773-			g
97 90 21 <b>NEW</b>	062134		Cable Connectors style and description as per Article-No. (25 pcs. each) 97 99 01 / 02 / 14 / 15 / 16 / 17 / 18 / 34 / 35 (20 pcs. each) 97 99 21 / 22 / 36	1420
97 90 22 <b>NEW</b>	062141			1550
97 90 23 <b>NEW</b>	062158		200 pcs. each 0.5 / 0.75 / 1.0 / 1.5 / 2.5 mm <sup>2</sup> 100 pcs. each 4.0 / 6.0 mm <sup>2</sup>	1220
97 90 24 <b>NEW</b>	062394		200 pcs. each 0.5 / 0.75 / 1.0 / 1.5 / 2.5 mm <sup>2</sup> 100 pcs. each 4.0 / 6.0 mm <sup>2</sup> / 50 pcs. 10.0 mm <sup>2</sup>	1355

## Contents of the established assortments in new TANOS MINI-systainers

Article-No.	EAN-Code	Pliers	Connectors	
	4003773-			g
97 90 00	025375		Cable Connectors (25 pcs. each) style and description as per Article-No. 97 99 01 / 02 / 04 / 07 / 09 / 14 / 16 / 17 / 20 / 21 / 34 / 35	1450
97 90 01	025382			1180
97 90 05	025535		200 pcs. each 0.5 / 0.75 / 1.0 / 1.5 / 2.5 mm <sup>2</sup> 150 pcs. each 4.0 / 6.0 mm <sup>2</sup> ; 50 pcs. each 10.0 / 16.0 mm <sup>2</sup>	945
97 90 06	025542		200 pcs. each 0.5 / 0.75 / 1.0 / 1.5 mm <sup>2</sup> ; 150 pcs. 2.5 mm <sup>2</sup> 75 pcs. each 4.0 / 6.0 mm <sup>2</sup> ; 50 pcs. 10.0 mm <sup>2</sup> ; 40 pcs. 16.0 mm <sup>2</sup>	1015
97 90 07	026877		500 pcs. each 0.5 / 0.75 / 1.0 / 1.5 / 2.5 mm <sup>2</sup>	830
97 90 08	026990		300 pcs. each 0.5 / 0.75 / 1.0 / 1.5 mm <sup>2</sup> 200 pcs. 2.5 mm <sup>2</sup>	840
97 90 09	028574		200 pcs. each 0.5 / 0.75 / 1.0 / 1.5 / 2.5 mm <sup>2</sup> 100 pcs. each 4.0 / 6.0 mm <sup>2</sup> ; 50 pcs. 10.0 mm <sup>2</sup>	1170
97 90 10	046202		200 pcs. each 0.5 / 0.75 / 1.0 / 1.5 / 2.5 mm <sup>2</sup> 100 pcs. each 4.0 / 6.0 mm <sup>2</sup> ; 50 pcs. 10.0 mm <sup>2</sup>	1360
97 90 12	048916		200 pcs. each 0.5 / 0.75 / 1.0 / 1.5 / 2.5 mm <sup>2</sup> 100 pcs. each 4.0 / 6.0 mm <sup>2</sup> ; 50 pcs. 10.0 mm <sup>2</sup>	1430



# 97

## 97 Crimping Pliers "PreciForce"



97 52 36



97 52 38



97 52 30



97 52 33










97 52 34



97 52 35



97 52 50



- ▶ for solder-free electrical connections
- ▶ repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- ▶ these tools have been set precisely (calibrated) in the factory
- ▶ high transmission of force thanks to lever action for fatigue-reduced working
- ▶ good handling thanks to favourable handle position, low weight, short design and ergonomically shaped handles
- ▶ all stressed parts are made of special steel, oil-hardened and tempered
- ▶ head burnished, two-colour dual component handles

**KNIPEX** special

The new Crimping Pliers provide a very good handling and amazingly high leverage despite the compact size. Particularly favourable for larger cross sections.



several boxes can be connected with each other

Article-No.	EAN-Code	Range of Application	Capacity		Length		g
			mm <sup>2</sup>	AWG	mm	g	
97 52 30	051855	non-insulated butt connectors	1.5-10.0	15-7	220	490	
97 52 33	051862	non-insulated terminals and plug connectors	0.5-10.0	20-7	220	490	
97 52 34	051879	non-insulated 4.8 mm	0.1-2.5	27-13	220	490	
97 52 35	051886	open plug-type 6.3 mm connectors	0.5-6.0	20-10	220	490	
97 52 36	051893	insulated terminals and connectors	0.5-6.0	20-10	220	490	
97 52 38	051909	end sleeves (ferrules)	0.5-6.0	20-10	220	490	
97 52 50	051916	COAX-BNC-Connectors RG 58, 174, 188, 316			220	490	
97 49 94	030947	locator for 97 52 34					
97 49 95	031000	locator for 97 52 35					




# 12 "Multistrip 10", Self-Adapting Universal Insulation Stripper

patented



12 42 195




Wire cutter for multiple stranded wire cables up to 10.00 mm<sup>2</sup>


- ▶ fully automated adjustment to the respective cross-section-dependent insulation thicknesses in a range from 0.03 – 10.0 mm<sup>2</sup>
- ▶ the so far common fine adjustment of the tool is no longer necessary due to the unique self-feeding of the cutting depth preventing damage to the conductor
- ▶ the steel-made restrain jaws with integrated cutting edges very often also allow professional stripping of cables with demanding insulating materials like Teflon® and Radox®
- ▶ with wire cutter for copper and aluminium wires, multiple stranded up to 10 mm<sup>2</sup> and single stranded up to 6 mm<sup>2</sup>
- ▶ smoothly operating mechanism
- ▶ easily interchangeable screw-on style blades, length stop and restrain jaws with cutting edges

## KNIPEX special


The cutting edges at the steel clamping jaws (1) firmly restrain the insulated cable and avoid skidding. The stripping blades (2) cut to the correct depth and remove the insulation cleanly without any manual adjustment.




Article-No.	EAN-Code	Stripping capacities			g
		Length mm	mm <sup>2</sup>	AWG	
12 42 195	054580		0.03-10.0	32-7	300
12 49 21	057581		spare blades		
12 49 22	057598		spare clamping jaws		
12 49 23	057604		spare length stop		



Steel restrain jaws with cutting edges avoid skidding of the cable



Precise stripping from 0.03 up to 10.0 mm<sup>2</sup>



Opens automatically once the stripping operation is completed

- ▶ body made of tough fibreglass reinforced plastic
- ▶ ergonomic soft compound zone in the handle area for a secure grip

Teflon® is a registered trademark of E. I. du Pont de Nemours and Company

Radox® is a registered trademark of Huber & Suhner AG

Distributed by:

L100 01705/01/02.06/7.000/GB

### KNIPEX-Werk C. Gustav Putsch KG

Oberkamper Straße 13  
42349 Wuppertal  
Germany

Phone: +49 202 47 94-0  
Fax: +49 202 47 74 94

Internet: [www.knipex.de](http://www.knipex.de)  
E-Mail: [info@knipex.de](mailto:info@knipex.de)