Product Information

2470PJI050P30

EAN 4031582010077

Swivel castor, Housing made of pressed steel, zincchromatised, double ball bearing swivel head, axle riveted.

Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey nonmarking, plain bearing, bolt hole

Castors can be mounted with standard screws; various length screws can be used..

Wheel diameter	50 mm
Width of Tread	19 mm
Centre hole	11 mm
Offset	24 mm
Swivel Interference	98 mm
Overall height	69 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.139 Kg / daN
Dynamic Load capacity	50 Kg / daN
Static Load capacity	100 Kg / daN
Swivel Radius	49 mm
Hardness of tread	A 87 Shore



Versions:





