TP-LINK[®]

450Mbps Wireless N Access Point TL-WA901ND

• Features

- Wireless N speed up to 450Mbps makes it ideal for bandwidth consuming or interruption sensitive applications like video streaming, online gaming and VoIP calling
- Backward compatible with 802.11b/g products
- MIMO[™] technology provides robust high-bandwidth wireless Tx/Rx capability at further range
- Supports multiple operating modes (Access Point, Client, Universal/WDS Repeater, Point to Point, Point to Multi-point)
- WPA/WPA2 encryptions provide your network with active defense against security threats
- Supports Wi-Fi Multimedia (WMM) assures the quality of VoIP and multimedia streaming
- Up to 30 meters (100 feet) of flexible deployment with included Passive Power over Ethernet Injector
- Up to 4 SSIDs and VLAN support, it allows networks administrator to segregate different services or applications to different designated users
- External detachable antennas allow for better alignment and stronger antenna upgrades
- Wall mounted available, also can be placed horizontally on a table or desk



• Description

The TP-LINK Wireless N Access Point TL-WA901ND is designed to establish or expand a scalable high-speed wireless N network or to connect multiple Ethernet enabled devices such as game consoles, digital media adapters, printers, or network attached storage devices to a wireless network. The AP supports a host of different functions that makes your wireless networking experience more flexible than ever before. Now, you can enjoy a better Internet experience when downloading, gaming, video streaming or with any other application that you may wish to use.

www.tp-link.com

• Specifications

HARDWARE FEATURES	
Interface	1 * 10/100M Ethernet Port (RJ45)
	Support Passive PoE
Button	Power On/Off Button
	WPS Button
	Reset Button
External Power Supply	12VDC / 1A
Wireless Standards	IEEE 802.11n, IEEE 802.11g, IEEE 802.11b
Dimensions (Wx Dx H)	7.67*5.12*1.43 in.(194.82*129.93*36.2mm)
Antenna Type	3*5dBi Detachable Omni Directional (RP-SMA)
WIRELESS FEATURES	
Frequency	2.4-2.4835GHz
Signal Rate	11n: Up to 450Mbps(dynamic)
	11g: Up to 54Mbps(dynamic)
	11b: Up to 11Mbps(dynamic)
EIRP	<20dBm(EIRP)
	270M: -68dBm@10% PER
Reception Sensitivity	130M: -68dBm@10% PER
	108M: -68dBm@10% PER
	54M: -68dBm@10% PER
	11M: -85dBm@8% PER
	6M: -88dBm@10% PER
	1M: -90dBm@8% PER
	Access Point
	Repeater (Range Extender)
Wireless Modes	Bridge with AP
	Client
	Multi-SSID
Wireless Functions	Enable/Disable Wireless Radio
	WDS Bridge
	MAC Address Filter
Wireless Security	64/128/152-bit WEP, WPA/WPA2, WPA-PSK/WPA2-PSK
Quality of Service	WMM
Management	SNMP
Advanced Functions	Up to 30 meters Passive PoE is supported

www.tp-link.com

a product names are eans or used to make

OTHERS	
Certification	CE, FCC, RoHS
System Requirements	Microsoft Windows 98SE, NT, 2000, XP, Vista™ or Windows 7/8,
	MAC OS, NetWare, UNIX or Linux.
Environment	Operating Temperature: 0°C~40°C (32°F~104°F)
	Storage Temperature: -40°C ~70°C (-40°F~158°F)
	Operating Humidity: 10%~90% non-condensing
	Storage Humidity: 5%~90% non-condensing

• Diagram:



www.tp-link.com