


## MKDS 1/ 2-3,5

Order No.: 1751248

The figure shows a 10-position version of the product



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1751248>

PC terminal block, Nominal current: 10 A, Nom. voltage: 160 V,  
Pitch: 3.5 mm, Number of positions: 2, Type of connection: Screw  
connection, Assembly: Soldering, Conductor/PCB connection  
direction: 0 °, Color: green

### Commercial data

|                          |                   |
|--------------------------|-------------------|
| EAN                      | 4017918028329     |
| Pack                     | 50 pcs.           |
| Customs tariff           | 85369010          |
| Weight/Piece             | 0.001151 KG       |
| Catalog page information | Page 49 (CC-2007) |

### Product notes

WEEE/RoHS-compliant since:  
01/01/2003



<http://www.download.phoenixcontact.com>  
Please note that the data given  
here has been taken from the  
online catalog. For comprehensive  
information and data, please refer  
to the user documentation. The  
General Terms and Conditions of  
Use apply to Internet downloads.

### Technical data

#### Dimensions / positions

|                     |        |
|---------------------|--------|
| Pitch               | 3.5 mm |
| Dimension a         | 3.5 mm |
| Number of positions | 2      |

|                        |              |
|------------------------|--------------|
| Pin dimensions         | 0,5 x 0,9 mm |
| Hole diameter          | 1.1 mm       |
| Screw thread           | M2           |
| Tightening torque, min | 0.22 Nm      |
| Tightening torque max  | 0.25 Nm      |

**Technical data**

|                                    |                   |
|------------------------------------|-------------------|
| Insulating material group          | I                 |
| Rated surge voltage (III/3)        | 2.5 kV            |
| Rated surge voltage (III/2)        | 2.5 kV            |
| Rated surge voltage (II/2)         | 2.5 kV            |
| Rated voltage (III/2)              | 200 V             |
| Rated voltage (II/2)               | 400 V             |
| Connection in acc. with standard   | EN-VDE            |
| Nominal current $I_N$              | 10 A              |
| Nominal voltage $U_N$              | 160 V             |
| Nominal cross section              | 1 mm <sup>2</sup> |
| Maximum load current               | 12 A              |
| Insulating material                | PA                |
| Inflammability class acc. to UL 94 | V0                |
| Stripping length                   | 5 mm              |

**Connection data**

|                                                                            |                      |
|----------------------------------------------------------------------------|----------------------|
| Conductor cross section solid min.                                         | 0.14 mm <sup>2</sup> |
| Conductor cross section solid max.                                         | 1.5 mm <sup>2</sup>  |
| Conductor cross section stranded min.                                      | 0.14 mm <sup>2</sup> |
| Conductor cross section stranded max.                                      | 1 mm <sup>2</sup>    |
| Conductor cross section stranded, with ferrule without plastic sleeve min. | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule without plastic sleeve max. | 0.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule with plastic sleeve min.    | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.    | 0.5 mm <sup>2</sup>  |
| Conductor cross section AWG/kcmil min.                                     | 26                   |
| Conductor cross section AWG/kcmil max                                      | 16                   |
| 2 conductors with same cross section, solid min.                           | 0.14 mm <sup>2</sup> |

|                                                     |                      |
|-----------------------------------------------------|----------------------|
| 2 conductors with same cross section, solid max.    | 0.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded min. | 0.14 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded max. | 0.2 mm <sup>2</sup>  |

#### Certificates / Approvals



Certification

CB, CCA, CSA, CUL, GOST, SEV, UL

#### CSA

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
| Nominal current $I_N$ | 10 A  |
| AWG/kcmil             | 28-16 |

#### CUL


|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
| Nominal current $I_N$ | 10 A  |
| AWG/kcmil             | 30-16 |

#### UL


|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
| Nominal current $I_N$ | 10 A  |
| AWG/kcmil             | 30-16 |

## Drawings

### Drilling diagram



### Dimensioned drawing



**Address**

PHOENIX CONTACT AB  
Linvägen 2  
S-14144 Huddinge, Sweden  
Phone +46/8/608-64-00  
Fax +46/8/608-64-99  
<http://www.phoenixcontact.se>



© 2009 Phoenix Contact  
Technical modifications reserved;