




THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS: ANGLE X.° ± 1°
UNIT: MM X.X ± 0.5°
X.X ± 0.35
X.XX ± 0.25
X.XXX ± 0.15





NOTES:

1.CHARACTERISTICS:

- 1.1. RATED VOLTAGE:250V.
- 1.2. RATED CURRENT:3AMP.
- 1.3. CONTACT RESISTANCE: 35mohms MAX.INITIAL.
50mohms MAX.AFTER.
- 1.4. INSULATION RESISTANCE:1000mohms MIN.at 500V DC.
- 1.5. DIELECTRIC STRENGTH:500VRMS
- 1.6. OPERATING TEMPERATURE RANGE:-55°C~85°C.
- 1.7. INSERTION/EXTRACTION FORCE PER CONTACT:340g Max./21g Min

2.MATERIAL:

- 2.1. INSULATORS:PBT+30% G.F(UL94V-0) BLACK.
- 2.2. CONTACTS:BRASS C2800R-H,GOLD(G/F)TOP OVER CONTACT AREA, 100u" Min MATTE-TIN TOP OVER SOLDER AREA,50u"Min NICKEL UNDER PLATE.
- 2.3. FRONT SHELL:SPCC,100u" Min BRIGHT TIN TOP OVER.50u" Min COPPER UNDER PLATE.
- 2.4. BACK SHELL:SPCC,100u" Min BRIGHT TIN TOP OVER,50u"Min COPPER UNDER PLATE.



Ordering	Dimensions(mm)				
Part Number	SIZE	A±0.25	B±0.25	C±0.25	D±0.25
MHDD09-F-T-B-S	09	30.81	24.99	16.92	19.28
MHDD15-F-T-B-S	15	39.25	33.32	25.25	27.75
MHDD25-F-T-B-S	25	53.03	47.04	38.96	41.30
MHDD37-F-T-B-S	37	69.50	63.50	55.42	57.40

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN Johnny		DATE 08-06-13	
APPROVED		DATE	
SCALE	SHEET OF 1 OF 1	REV: 3.0	
DRAWING No MHDDXX-F-T-B-S			



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR RoHS COMPLIANCY.



MH CONNECTORS LTD.