





MODEL 6115

The AirForce Ionizing Blow-off Gun was designed with the operator in mind. The AirForce's lightweight, flexible air hose—just 3/8" in diameter—moves with the operator and makes work easier. No high voltage cable means improved operator safety. The gun's ergonomic design—with a light touch trigger and easy-view LED—minimizes fatigue and eliminates wrist hyperextension. The compact console can be mounted anywhere, so it doesn't take up valuable workspace but is still easily accessible. To make the work environment more pleasant, the AirForce also features low audible noise.

Strong blow-off power makes the AirForce effective in removing particle contamination. Steady-state DC ion emission provides efficient ionization with an average discharge time of less than 1.0 second. Results are even better because Ion's patented IsoStat technology¹ means static charge is controlled with constantly balanced ionization.

Features and Benefits

- Ergonomic gun design
- Flexible, lightweight air hose with integral low voltage power cable
- Replaceable emitter point
 assembly and quick-eject filter
- Strong blow-off force
- Steady-state DC ion emission
- IsoStat® technology
- Durable static-dissipative materials
- 1. U.S. Patent No. 5,055,963

- · Reduces fatigue and wrist hyperextension
- Moves with operator and does not interfere
 with work
- Minimizes maintenance downtime
- Effective removal of particle contamination
- Fast discharge times; efficient ion delivery
- Intrinsically balanced; no calibration needed
- Holds up to high impact; ESD-safe



Ion Systems

Specifications

AirForce Ionizing Blow-off Gun Model 6115		
Audible noise	70 dBA at @ 1m, 30 psi	
Conducted EMI	29 dbµV; Average level 100 KHz to 1.1 MHz $$	
Ozone	<0.005 ppm (24-hour accumulation); conforms to OSHA requirements	
Blow-off force	41 grams at 30 psi; measured at 3" (7.6 cm) from a 2" (5.1 cm) diameter target	
Discharge time	±1000-100V 1.0 seconds at 6" (15.2 cm), 30 psi, Tested in accordance with ANSI/ESD STM3.1-2000	
lon balance	±30 volts	
Construction	<i>Gun and console:</i> Static-dissipative polycarbonate <i>Gun hanger:</i> 302 stainless steel; optional mounting stand for hands-free operation	
Console power requirements	24 VAC, 10 watts powered from wall transformer	
Indicators	Green LED on both console and gun	
lon emission	Steady-state DC	
Emitter points	Tungsten emitter points	
Airhose	Static-dissipative polyurethane, 3/8" outside diameter; 7' (2.1m)/65 psi	
Console gas input	20-65 psi, Clean Dry Air (CDA) or nitrogen	
Gas connection	1/4" male industrial interchange quick disconnect	
Gas air filter	99.9% efficient, 0.1 micron or larger	
Mounting	Metal mounting plate attaches to back of console	
Dimensions	<i>Gun:</i> 8L x 3W x 1D inches (20.3L x 7.6W x 2.5D cm) <i>Console:</i> 8.5L x 3.0W x 1.6D (21.6L x 7.6W x 4.1D cm)	
Weight	<i>Gun:</i> 12 oz (341g) with 7' (2.1m) air hose <i>Console:</i> 11.5 oz (326 g)	
Warranty	2 year limited warranty	
Certifications		



The AirForce is lightweight, flexible and easy-to-use. With strong blow-off power the AirForce is effective in removing particle contamination

High Reliability

IsoStat technology also guarantees that the AirForce is calibration-free and requires little maintenance when used with CDA or nitrogen. When the air filter or emitter points need replacement, they snap in and out in less than a minute—reducing gun down-time and improving long-term performance. To avoid replacement costs, the AirForce is made from durable polycarbonate that holds up to high impact. The gun body, air hose and control console are static-dissipative and ESD-safe. And an extremely low EMI level ensures the AirForce won't interfere with other electronic equipment or operations.

Patented IsoStat Technology

Ion's patented IsoStat technology is the first balancing technology for ionizers to guarantee intrinsically balanced ionization and elimination of complicated feedback circuits. IsoStat is based on a law of physics, Conservation of Charge, which states that charge cannot be created or destroyed in an isolated system. By isolating the ionizer's emitter points from ground, IsoStat ensures equal numbers of positive and negative ions. Characteristics of IsoStat ionizers include:

• Ionizers never need calibration and require very little maintenance

· Small size and operation without grounding wires



 1750 North Loop Road, Alameda, CA 94502

 Tel:
 510.217.0600 or 800.367.2452

 Fax:
 510.217.0484

 info@ion.com, www.ion.com
 DS-6115 - Ver. 2

DS-6115 - Ver. 2 © 2006 Ion Systems, Inc. All rights reserved.

Ordering Information

91-6115-NXFMR	Model 6115 AirForce Gun, 8 ft hose
33-6115	Optional gooseneck mounting stand
91-6115SWT	Optional footswitch
14-1306	100 VAC transformer
14-1310	120 VAC wall transformer
14-1523	230 VAC transformer