

Elpress Mobile



Mobile Box,

Box for the Mobile tool which has place for the tool and 5-6 dies. The Mobile tool and dies is ordered separately.

- a professional crimp tool with interchangeable dies

A complete crimping tool solution does not have to be a heavy load to carry. **Elpress Mobile** has a wide range of interchangeable dies which enables the user to only have one tool. The tool is designed for electrical installation engineers who require a good hand tool – reliable, practical, safe, economical and comfortable to use – readily in a tool box.

- Parallel-action stroke, tested for 20000 cycles, generates a maximum force of 10000 N
- Easily interchangeable crimp dies are kept together with a special rod to simplify handling
- A wide range of crimping dies enables the user to cover all applications in just one tool frame
- Length 234 mm, height 64 mm, width 24 mm, weight 460 g

You purchase Elpress Mobile in three basic performances

1. Elpress Mobile, Mobile hand tool (only the frame).

2. Mobile Installation,

Mobile hand tool and two interchangeable dies: OAA0525, for crimping of insulated terminals, 0.5 - 2.5 mm². OEB0210, for crimping of end sleeves 0.25 - 10 mm².

3. Mobile DataCom,

Mobile hand tool and two interchangeable dies: OMP45, for crimping of modular plug, RJ45 contacts. OCC1113, for crimping of coaxial contacts RG58, 59, 62, 71.





Elpress Mobile

You complete your kit with these dies:



OAA0160 For crimping of pre-insulated terminals 0.1 - 0.5



OAA0525 For crimping of pre-insulated terminals 0.5 - 2.5 mm².



OPB0140 For crimping of global power connectors, GPC.



OPB6099 For crimping of global power connectors, GPC.



OWB4099 For W-crimping of un-insulated terminals 4 - 10 mm².



OKB0725 For indent crimping of un-insulated terminals 0.75 - 2.5 mm².



OKB0560 For indent crimping of un-insulated terminals 0.5 - 6 mm².







OEB0210 For crimping of end terminals 0.25 - 10 mm².

ORB0110

For roll crimping of terminals

0.1 - 1.0 mm².



For crimping of



OEB3550 For crimping of end terminals 35 - 50 mm².







OMP45 For crimping of modular-



plug RJ45.

OMP11 For crimping of modularplug RJ11.

ORB0560 For roll crimping

of terminals

0.5 - 6 mm².



OCC0908 For crimping of coaxial contacts.



OCC1113 For crimping of coaxial contacts.

OCC4755 For crimping of coaxial contacts.



Elpress AB • P.O. Box 186 • SE-872 24 KRAMFORS, Sweden Tel: +46 612 71 71 00 • Fax: +46 612 71 71 51 E-mail: sales@elpress.se • www.elpress.net

