

digimax and calimax.



411 170 1 Digital Calliper digiMax, Reading 0.01 mm.

Material: Non-metallic high-tech material with 60% fibre-glass content.
 Scale: 5-digit digital display with 7.5 mm numeral height for easy reading.
 Reading: 0.01 mm as well as 0.0005 inch.
 Packaging: Plastic box with hanging attachment.
 Standards: CE compliant.
 Application: For outside, inside, depth and step measurements.
 Extra: Switches off automatically after 5 minutes of non-use.
 Zero setting possible in every position for quick comparison measurements. Battery with approx. 2-year service life included.

Order-No.	150	6	48	5
29422 9				

dialMax and dialMax ESD.



411 210 2 Analog Calliper dialMax, Reading 0.1 mm.

Material: Non-metallic high-tech material with 60% fibre-glass content.
 Scale: Dial, diameter 35 mm.
 Reading: 0.1 mm; 1 dial rotation represents 10 mm.
 Accuracy as per DIN 862.
 Packaging: Blister Packed.
 Application: For outside, inside, depth and step measurements.
 Extra: Impact resistant dial can be recalibrated to zero.

Order-No.	150	6	45	5
27082 7				



411 320 3 Vernier Calliper caliMax, Reading 0.1 mm.

Material: Non-metallic high-tech material with 60% fibre-glass content.
 Scale: Vernier for millimetre and inch display.
 Reading: 0.1 mm as well as 1/64 inch.
 Accuracy as per DIN 862.
 Packaging: Blister Packed.
 Application: For outside, inside, depth and step measurements.
 Extra: Almost parallax-free reading of the measurement value.
 Neon green vernier scale in with strong contrast for optimal reading.

Order-No.	150	6	45	10
27083 4				




411 210 8 Dial Calliper dialMax ESD, Reading 0.1 mm.


Material: Calliper made of ESD-safe material.
 Scale: Dial, diameter 35 mm.
 Reading: 0.1 mm; 1 dial rotation represents 10 mm.
 Accuracy as per DIN 862.
 Packaging: Blister Packed.
 Standards: IEC 61340-5-1.
 Application: For use with electrostatically sensitive components.
 For outside, inside, depth and step measurements.
 Extra: Now possible: measurements in ESD protection zones.
 Impact resistant dial can be recalibrated to zero.

Order-No.	150	6	45	5
31439 2				


Wiha Info




Outside measuring



Inside measuring



Step measuring



Depth measuring