

## NOXLITE SMART SPOT

### Outdoor LED wall luminaires



#### Areas of application

- Driveways
- Garages
- Terraces
- Paths
- Gardens

#### Product benefits

- Smart grouping with master/slave arrangement
- Flexible direction of light thanks to movable luminaire heads
- Energy-efficient thanks to LED technology
- Easy installation with fast connection

#### Product features

- Type of protection: IP55
- Invisible integrated high-frequency and light sensor



# Product family datasheet

## Technical data

Product description	Electrical data				Photometrical data				Dimensions & weight	
	Nominal wattage	Nominal voltage	Mains frequency	Operating mode	Color temperature	Luminous flux	Light color (designation)	Color rendering index Ra	Width	Height
NOXLITE SMART SPOT SINGLE	7 W	220...240 V	50/60 Hz	ECG	3000 K	520 lm	Warm white	>80	86.0 mm	200.0 mm
NOXLITE SMART SPOT DOUBLE	13 W	220...240 V	50/60 Hz	ECG	3000 K	545 lm	Warm white	>80	179.0 mm	200.0 mm

Product description	Colors & materials				Temperatures & operating conditions	Additional product data	Capabilities
	Body material	Product color	Cover material	Reflector material	Ambient temperature range	Number of lighting outlets	Type of installation
NOXLITE SMART SPOT SINGLE	Aluminum	White	Polykarbonát (PC), UV stabilizace	Polycarbonate (PC)	-20...+40 °C	1	Direct mounting/Surface-mounted
NOXLITE SMART SPOT DOUBLE	Aluminum	White	Polykarbonát (PC), UV stabilizace	Polycarbonate (PC)	-20...+40 °C	2	Direct mounting/Surface-mounted

Product description	Type of connection	Certificates & standards		Country specific categorizations
		Protection class	Type of protection	Order reference
NOXLITE SMART SPOT SINGLE	Terminal, 2-pole, max. 2,5 mm <sup>2</sup>	II	IP55	NOXLITE SMART S
NOXLITE SMART SPOT DOUBLE	Terminal, 2-pole, max. 2,5 mm <sup>2</sup>	II	IP55	NOXLITE SMART D

## Application advice

For more detailed application information and graphics please see product datasheet.

## Product family datasheet

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899934313	NOXLITE SMART SPOT SINGLE	Shipping carton box 4	250 mm x 200 mm x 270 mm	13.50 dm <sup>3</sup>	3009.00 g
4052899934320	NOXLITE SMART SPOT DOUBLE	Shipping carton box 4	422 mm x 222 mm x 270 mm	25.29 dm <sup>3</sup>	4191.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.