## Wiha MagicRing<sup>®</sup> hexagon L-key.

Securely holds hexagon bolts in place in any position.

MagicRing<sup>®</sup> holds all standard screws!

- DIN 6912
- DIN 7984
- DIN EN ISO 4762
- DIN EN ISO 10642 • DIN EN ISO 4026
- DIN EN ISO 4028
- DIN EN ISO 4027
- DIN EN ISO 4029
- DIN EN ISO 7380

Wiha hex keys with MagicRing<sup>®</sup> guarantee the perfect location of hex screws in every position.

Due to a high-quality retaining ring in the key head, the insertion of a screw in straight, inclined or very deep pocket holes is no problem. The new ball geometry with MagicRing<sup>®</sup> now offers even more advantages:

Greater retention force for screws. For example, size 6 holds screws up to 1000 mm in length.
Enlarged maximum torque of up to 10% due to the new ball geometry.

• Can now be used with all standard screws.

A further advantage is that the Wiha MagicRing<sup>®</sup> can even be used to hold non-magnetisable screws made of stainless steel, titanium and aluminium.



Wiha MagicRing<sup>®</sup> metric is only available as long design from size 3.

With the inch dimensions, MagicRing<sup>®</sup> is available from 1/8". All series are made from highquality chrome-vanadium steel. Thanks to the Wiha MagicRing®, inserting and removing screws is safe and easy, even in areas that are difficult to access.



The ball end can be rotated by up to 25° in both clockwise and anti-clockwise direction.

## ⊥ → Wiha MagicRing® hexagon L-key.

- Suitable for removing sunkhead standard screws and for inserting and working screws in horizontal, inclined of deep pocket holes
- Holds screws made of steel and non-magnetisable materials such as stainless steel, titanium and aluminium
- Ideal for applications where there is insufficient space for a simple hex key
- No troublesome searching for dropped screws



## For Allen screws (metric).

	ci							
369	Ball er	nd hex L-ke	y, long.					
Blade:	Chrome-vanadium steel, through hardened, chrome-plated.							
Standards:	Based on ISO 2936L.							
Application:	Especially for screws that are difficult to access.							
Extra:	The ball end enables the user to work at angles up to 25°.							
	-							
Order-No.	۲			<b>—</b>				
01392	1.5	91	15	10				
01393	2	101	18	10				
01395	2.5	113	20	10				
01396	3	128	23	10				
01398	4	142	29	10				
01400	5	163	33	10				
01402	6	184	38	10				
07922	7	195	39	5				
01404	8	206	44	10				
36452	9	217	47	5				
01406	10	231	50	5				
01408	12	259	57	5				

## For Allen screws (metric).



 

 Ball end hex L-key set in ProStar.

 Chrome-plated, 9 pcs.

 Blade:
 Chrome-vanadium steel, through hardened, chrome-plated.

 Standards:
 Based on ISO 2936L.

 Application:
 Especially for screws that are difficult to access.

 Extra:
 Space saving ProStar allows the easy removal of each key without moving any others. The ball end enables the user to work at angles up to 25°.

 Order-No.
 Series

Order-No.	Selles						
07185	369 S9						5
۲	369	1.5	2	2.5	3	4	
		5	6				

