300 W

0 to 150 V

0 to 60 A

EL34243A

120 A

300 W

0 to 150 V

0 to 60 A

0.02% + 15 mV

# Keysight EL30000 Series DC Electronic Loads

### Measure, capture and display

The EL30000 Series bench DC electronic loads provide superior performance in compact bench form factor. A single and dual-channel model is available with up to 600 W – ideal for design verification of consumer power supplies, batteries, battery modules, solar panels, LED drivers, and power converters. You can easily characterize wide-bandgap semiconductor components such as MOSFET and IGBT.

The EL30000 Series bench DC electronic loads are fully SCPI programmable with built-in USB, LAN, and optional GPIB interfaces. Advance features include scope view, data logging, sequencing, and more, enabling you to measure, capture, and quickly display your results.







EL34243A 600 W dual-input bench electronic load 150 V, 60 A

Option	Description	
EL34GPBU	GPIB user-installable interface module	
UK6	Commercial calibration with test result data	
SEC	NISPOM and file security	

Parallel mode current		NA	120 A
Typical minimum operating voltage at full scale current		1.5 V	
Command processing time		< 10 ms	
Programming Accu	uracy ± (% of output + offset)		· ·
Constant current (CC) mode	Low, 0.6 A	0.04% + 130 uA	
	Medium, 6 A	0.04% + 2 mA	
	High, 60 A		0.04% + 12 mA
Constant voltage (CV) mode	Low, 15 V	0.02% + 3 mV	
	High, 150 V	0.02% + 15 mV	
Constant resistance (CR) mode	Low, 0.05 $\Omega$ to 30 $\Omega$	0.1% + 230 mS	
	Medium, 10 $\Omega$ to 1.25 k $\Omega$	0.1% + 18 mS	
	High, $100~\Omega$ to $4~k\Omega$	0.1% + 3.5 mS	
	Ultra-high, 250 $\Omega$ to 100 k $\Omega$		0.1% + 400 uS
Constant power (CP) mode	Low, 0.02 W – 8 W <sup>1</sup> / 7 W <sup>2</sup>	0.06% + 4 mW	
	Medium, 0.3 W – 35 W <sup>1</sup> / 30 W <sup>2</sup>	0.06% + 260 mW	
	High, 2 W – 350 W <sup>1</sup> / 300 W <sup>2</sup>		0.06% + 1.6 W
Programming Accu	uracy ± (% of output + offset)		
Current	Low, 0.6 A		0.04% + 120 uA
	Medium, 6 A		0.04% + 1.8 mA
	High, 60 A	0.04% + 9.6 mA	
Voltage	Low, 15 V	0.02% + 3 mV	
Voltage			

EL34143A

350 W

1

0 to 150 V

0 to 60 A

NA

High, 150 V

**Performance specifications** 

Input ratings (0 to 40°C)

Parallel mode current

Input power

Channel

#### www.keysight.com/find/el30000



<sup>&</sup>lt;sup>1</sup> Power range of E34143A

<sup>&</sup>lt;sup>2</sup> Power range of E34243A

## **Key Values**

#### Measures accurately

- integrated voltmeter and ammeter
- precise programming / readback accuracy
- built-in 2-wire or 4-wire remote sense technology

# Captures, stores, and transfers dynamic waveforms

- data logger that is configurable
- · log voltage, current and energy
- internal or external memory storage
- export to .CSV for post analysis


#### Displays like an oscilloscope for precise analysis

- · performs precise transient analysis with scope function
- · digitizes voltage and current
- displays results on a 4.3-inch color LCD screen

#### Advanced characterization


- use operating modes: constant current (CC), constant voltage (CV), constant resistance (CR), constant power (CP)
- improve measurements with low current range
- dynamic load profiles with List (continuous, pulse, or toggle)
- adjust transient steps with programmable slew rate
- modern connectivity: LAN (LXI Core), USB and GPIB (optional)






















- 1. Front USB host port for external USB drive
- Color display shows readback voltage, current and power simplifying setup and monitoring
- Channel selection and control knobs for quick adjustments
- 4. Function keys and keypad provide intuitive interface
- Two electronic load inputs allow individual on/off control (EL34243A only)
- Color coded input channels, controls, and display allow at a glance verification
- 7. Rear output terminals for clean wiring in a system

- Optional GPIB
- 9. USB communication port
- 0. LXI LAN port
- 11. Digital I/O
- 12. Parallel input connection for 120 A, 600 W input (EL34243A)
- 13. Scope function captures transients
- 14. Data logger records seconds to hours
- 15. Transient LIST creates a dynamic load profile

Find us at www.keysight.com Page 2